



1.3 10000 10000 10000 1 3 755 808 1064

1600 / 1200 / 1000

! 35 * 12 20 * 12


.3 Dual- TEC

24

4.Long life:

Working Principle

Suits for all skin and hair types



- **755nm for white skin** (fine, golden hair removal)
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)







Different spot size Handle color optional



□□□□□ □□□□□ □□□□ □□□ □□□□□ □□□□□□□□□□

Alex 755nm □□□□□□□□ □□□□□□□□

□□□□□□□ □□□□□□□ □□□□□□□□ 808 □□□□□ □□□□□

□□□□□□□ □□□□□□□ □□□□□□□□ 1064 □□□□□□ □□□□□

Treatment effect



□□□□□□□□ □□□□□□□□

1. □□□□ □□□□ □□ □□□□ □□ □□□□ 6 □ □□□□□ □□ □□□□□□ 6 □ □□□□□ □□□□ □□□□ □□□□ □□□□ □ □□□□ □□□□□□□□ 6 .2 □□□□□□ □□□□ .3 OEM □□□□ / □□□□) □□□□□□□□...

