

Stronger, Faster

×

14-inch HD 4K Screen



000000 000

----- 0 000000 000000 000000 0000 0 000 0000 00 .000000 00000 0000 00 0000 00000 000000

----- 0000000000 0000000 0000000 00000000000 000000 0000 00000 00 000 00000000 000 000000 000000
0000000000...

----- 808 0000 0000000 00000nm 1064 755808 00nm 0 0000 0000 000000 000000 00000 000000.

---- 1 0000 10-1 0000000 .0000 000000 000000. Treement 000000 !!! -

NEW



NEW



NEW



.ﺩﺭﺍﺩﺍﻥ ﺩﺍﺩﺍﺩﺍﻥ ﺩﺍﺩﺍﺩﺍﺩﺍﺩﺍﺩﺍﻥ ﺩﺍﺩﺍﺩﺍﻥ ﺩﺍﺩﺍﺩﺍﻥ ﺩﺍﺩﺍﺩﺍﺩﺍﻥ ﺩﺍﺩﺍﺩﺍﺩﺍﻥ ﺩﺍﺩﺍﺩﺍﺩﺍﻥ ﺩﺍﺩﺍﺩﺍﺩﺍﻥ
ﺩﺍﺩﺍﺩﺍﻥ 24 ﺩﺍﺩﺍﺩﺍﻥ ﺩﺍﺩﺍﺩﺍﺩﺍﺩﺍﻥ ﺩﺍﺩﺍﺩﺍﺩﺍﻥ ﺩﺍﺩﺍﺩﺍﺩﺍﻥ ﺩﺍﺩﺍﺩﺍﺩﺍﻥ ﺩﺍﺩﺍﺩﺍﺩﺍﻥ!

Free to be yourself

1 minute of painless hair removal,
Feeling the comfort and coolness that
has never been seen before.

14-inch screen

2 year warranty + work 24 hours



□□□□□□ □□□

350g lightweight **handle**, more ergonomic

Available in **black or white**





} 35mm



before after

Large 3.5cm spot size, and integration of three wavelengths
Hair removal is quick, efficient and convenient




One minute cooling -21°C

Best **TEC Cooling** system
hair remover laser




laser rod imported from America.10million—40million shots.Permanent hair removal



755808 1064nm □□□□□□ □□□□□ □□□□ □□□□ □□□□□ □□□□□ □□□□□□□□□□ □□.

*. 100000000 00000000 00000000 00 000000 000000 0000 0000
(0000 0000 0000 0000) 0000 00000 40-10 *
10 *bar 12bar 16bar 0 00000 00 000000000.

* 1600 / 1200 / 1000 1000 1000 1000



□□□□□ □□□□□

Before and After

Traetment comparison





Customer feedback

Ratings&Reviews



m*****a
Georgia

Supplier Service: **Very satisfied** (5 stars)

06 Jan 2021

On-time Shipment: **Very satisfied** (5 stars)



New design 1600W diode laser 755 808 1064 diode la...



Big hug with Maggie, she is very kindness and professional. Weifang Mingliang Electronics Co., Ltd is the best supplier , with high quality and professional package.

If you also need laser machine, strongly recommend them.

0



A*****
Mexico

Supplier Service: **Very satisfied** (5 stars)

01 Jan 2021

On-time Shipment: **Very satisfied** (5 stars)



New design 1600W diode laser 755 808 1064 diode la...



estoy muy feliz con mi compra, me llevo mi pedido a tiempo con buen empaque, espero que todo marche bien.. Maggy una excelente persona y vendedora espero tener más compras a futuro gracias

0



M*****a

Supplier Service: **Very satisfied** (5 stars)

20 Jan 2021

On-time Shipment: **Very satisfied** (5 stars)



Professional high Power 1600W diode laser hair remo...



super

0



808nm .
*
14 *
Service OEM. *
*