

2021 Salon Queen

Trending Model 1600W Laser
4K Smart Screen

Newest Germany Tech
Super Ice Cooling, Pain-free
Get most comfortable treatment



□□□□ □□□□ □□□□ □□ □□□□ 102 □□ □□□□□□ □□□□□□ □□□□.

□□□□□□□□ □□□□□□ □□□□□□.

□□□□□□ □□□□




□□□□


- 1.3 □□□□ Yag 1064nm Diode 808nm Alex 755nm □ 3 □□□□□ □□□□ □□□□ □□□□ □□□□ 1 □□ □□□□□□□ □□□ 1600 / □□□ 1200 / □□□ 1000 □□□□ □□□□ :□□□□□ □□□□
- !□□□□□□ □□□□ □□□ □□□□ □□□□□ □ □□ 35 * 12 □ □□ 20 * 12 □□□□□ □□□□□ □□□□-2 □□□ □□ □□□□ □□□□□ □□□□□ :□□□□□□□ □□□□□.3 Dual- TEC □ □□□ □□□□□ □□□□□□ □□□□ □□□□ □□□□ □□□□ 24 □ □ □□□□□ □□□□□□□□□□
- 4.Long life: □□□□□□□□ □□□□□□ □□□□ □□□□



A natural



B energy absorbed by hair



C hair follicle died

□□□□□ □□□□□ □□□□ □□ □□□□□ □□□□□□□□□□

Alex 755nm □□□□□□□ □□□□□□□

□□□□□□□ □□□□□□□ □□□□□□□ 808 □□□□ □□□□□

□□□□□□□ □□□□□□□ □□□□□□□ 1064 □□□□□ □□□□□

Handle Details


Three Wavelengths Work Togher





12*20nm


755nm Laser
808nm Laser
1064nm Laser





12*35nm

755nm Laser
808nm Laser
1064nm Laser



□□□□ □□□□ □ □□□□□□□

1-808 □□□□□□□ 755 :□□□□□ 3 □□□□□ □□□□□ / □□□□□□ □□□□□□ □□□□□ □□□□ □□□□ :□□□□□□ □□□□□
 1 □□ 3 □□□□□□□□ 1064 □□□□□□□□□□
 □□ 35 * 12 □ □□ 20 * 12 :□□□□□□□ □□□□ .3

4. □□□□□□□□ □□□□□□□ □□□□□ □□□ 1600 □□□ 1200 □□□ 1000 □□□□□ □□□□ □□□□□□□□
 3.Cooling: □□□□□□ □□□□□□ □□□□□ 24 □ □□□□□□ □□□□□ □□ □□□□□□□□ □□□□□ □□□□□□□□



□□□□ □□ □□□□ □□□□

□□□□□□□ □□□□ Super TEC □□□□□ □□□□□ □□□□ □□□□□

□□□□□ □□□□ 22- □□□□□ □□□□ □□□□□

Before and After

Treatment comparison



