




Diode Laser

Permanent hair removal

Understand more

13 inch screen!
 10 inch screen!
 5.0 inch screen!

			
<p>14 inch Screen Size</p>	<p>3000W Input power</p>	<p>1-10HZ Frequency</p>	<p>755nm 808nm 1064nm Wavelength</p>

>>Machine 14-inch large screen
 >>3000W machine power to ensure the treatment effect

>>1-10Hz fast frequency and 15x25mm spot size ensures faster, smooth and effective treatment

>>808 single wave or 755nm/808nm/1064nm perfect triple wavelengths

>>Easy to operate Data Base system,can do the treatment by man mode and women mode,

□□□□□□ □□□□□□ □□□□ □□□□□□ □□□□□□ □□ □□□□□□ □□□ □□□□□□

>> Long life time More than 40 millions shots

□□□□□□□□ □□□□ □□□□□□□ □□□□□□ □□□□□□ □□□□ □□□□ □□□□□□.



>>Double filters to keep water quality

>>TEC cooling Air Cooling Water CoolingSemiconductor cooling

□ □□□□□ □□□□ °C 28- °C 26 □□□□□□ □□□□□□ □□□□ □□□ □□□□

24<< hours continues work

>>Easy to operate Data Base system,can do the treatment by man mode and women mode,

□□□□□□ □□□□□□ .□□□□□□ □□ □□□□□□□ □□□□□□ □□□□

□□□□ □□□□□□ □□□□□□

>> Long life time More than 40 millions shots

□□□□□□□□ □□□□ □□□□□□□ □□□□□□ □□□□□□ □□□□ □□□□□□.



- Safety
- Quick
- Cooling system
- Permanent hair removal
- Best thermostatic water cycle system

□□□□□□ □□□



before




after



before

after



One minute treatment

Before and after treatment



□□□□□□ □□□□□ □□□ □ □□□ □□□□□□ **350** □□□□□□ □□□□

>>12 pieces or 16 pieces Germany Dilas original laser bars,600/800W/1200W power is capable to meet all demands of hair removal on the whole body;

>>1-10Hz fast frequency and 15x25mm spot size ensures faster, smooth and effective treatment;

>>Super sapphire touch cooling system ensures painless and comfortable treatment.

1) □□ □□□□□ □□□□□□ □□□□□ □□□□□□ □□□□□

□□□□ **6** □□ □□□□ **(2**

□□□□□□ □□□□ □□ □□□□ □□□□□ □□□□□□ □□□□□ □□□□□ □□□□□□ □□□□□ □□□□□ **(3!**

