

Diode Laser



15 Bar **1800W** Handle

*Increase the treatment head of nasal hair
and treat small parts easily



.0000 000000 00000 00000 000

.000000 00000 00 000 000 00000 .0000 00 *

.000000 00000 00 000 000 00000 *

.000000 000 *

0 00000 000000 000000 00000000 *

0 00000000 1064 808 755 00 00000000 808 0000000 0000000 000000 000000 *

350g
Ultra light handle




12×36mm
Handle
1800W diode laser hair removal



12×24 mm
Handle
1200W diode laser hair removal

Three Waves 755nm 808nm 1064nm

755nm (Alexandrite) / 808nm (Speed) / 1064nm (YAG)
 .(808nm) 808nm
 1064nm (YAG) .






ALEX 755nm
For white skin
(fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)



Treatment Comparison





Emergency stop button

12 inch big screen
quick touch
easy operate

Diode laser handle

Vents

Plug