



□□□□

.□□□ 16——8 □□□□□□ □□ □□□□□□□□ □□□□□□ □□ □□□□□ □□□ □□□□ *
 .□□□□□□ □□□□□□ □□□□ □□ □□□□□ □□ □□□□□ □□□□□ □□□□□ □□□□□ 50 □□ □□□□ *
 □□□□□□ □□□□□ □□□□ □□□□□□ □□□□□ □□□□□□ □□□□□□ □□□□□□ □□□□□□ □□□□□□ 3 *





Arm hair removal

Lip hair removal

Face hair removal

Leg hair removal

Back hair removal

Underarm hair removal

Bikini hair removal

DIODE LASER

755/808/1064nm diode laser, for all type skin hair removal, painless



ADVANTAGE

- **PAINLESS:**755/808/1064nm diode laser for all type skin hair removal
- **FASTER:**Large area spot sliding operation
- **NO TRAUMA:**There is no trauma to skin tissue
- **SAFETY:**To avoid the light of the deputy to reduce the difficulty of operation



□□□□□□ □□□

1200 □□□□ □□□□□□□□ □□□□□ □□□ □□□ 1800 □ □□□

□□□□□□ □□□ □□□ 35 * 12 □□ 20 * 12

350 *

() *

800/1000/1200/1600W
50 Million Shots
 USA / Germany Imported Laser Bar

755nm+808nm+1064nm



ALEX 755nm
For white skin
 (fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
 (brown hair removal)



YAG 1064nm
For black skin
 (black hair removal)

• *Cooling effect* •

The handle is frosted for one minute,
making your treatment more comfortable and painless



Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.








14 Android Screen

1. Three wavelength diode laser.
2. Golden laser bars from German or USA improved, 40,000,000+ longer lifespan.
3. Safe, Fast, Painless, permanent
4. For all skin and hair style hair removal
5. 14.0 inch true color touch screen with 6 skin colors.



□□□□□	808 30 □□□□
□□□□□□ □□□	800 □ □□□ 16 ---- 8 □ □□□□□□□□□ □□□□□□□□ □□□□□□□□□□ / □□□□□□□□ □□ □□□□□□□□
□□□	14 4 □□□□K □□□□□□ □□□□ □□□□
□□□□□□ □□□□□	808nm 755 □□nm 808nm 1064nm
□□□□□□	50 □□□□ □□□□□
□□□□□	10 ~ 150 □□□□□□□□ □□□□ □ 2 □□ / □
□□□□□□	1-10 □□□□□
□□□□□□	□□□□□□ □□□□□□ □□□□□□ TEC □□□□□□ □□□□□□ □□□□□□ □□□□ □□□□□□ □□□□□□ □□□□□□ □□□□□□ □□□□ □□ □□□□□□□□
□□□	3500 □□□
□□□□□□ □□□	12 * 20 □□□□□□□□ □□ 35 * 12 □□ □□
□□□□□□□□ □□□□□	110 □□□□□□□□ □□□□ 50 / □□□□ 220 □□ □□□□ 60 / □□□□
□□□□□□ □□□□□	95 □□□
□□□□□□□□ □□□□□	105 □□□

Premium OEM Factories

High-performance manufacturing capacity
R&D capability for customization
Professional certifications and approvals



! 24 !!