

Soprano Ice Titanium

Painless hair removal. For you,for life!



808nm

808nm

808nm

808nm

808nm

808nm

350g
Ultra light handle



12×36mm

Handle

1800W diode laser hair removal



12×24 mm

Handle

1200W diode laser hair removal

808 nm diode laser hair removal handle with 36 * 12 / 24 * 12 mm window size
I-VI diode laser hair removal handle with 36 * 12 / 24 * 12 mm window size

Soprano



755

808

1064

3 Wavelengths

New breakthrough!



360° Rotatable
6.8×6.8mm



Handle


1200W diode laser hair removal


Improved Reach: **360° Rotatable**

Easily treat areas that are normally hard to reach, including the ears, nostrils and glabella.

□□□□□□ □□□□□□

Treatment Comparison





සමස්ත පිරිසට පිරිසට

සමස්ත පිරිසට 14 .1

සමස්ත පිරිසට පිරිසට පිරිසට පිරිසට 6 6 6 .2

සමස්ත පිරිසට පිරිසට 6 .3

සමස්ත පිරිසට .4 OEM (පිරිසට / පිරිසට / පිරිසට / පිරිසට) පිරිසට...)

14inch true touch screen
6 kinds skin type for choice. accept ODM OEM Service.



Advantage of: soprano ice laser hair removal machine

Super cooling: air + water+TEC condenser cooling system,
Which keep water temperture in 25-28°C,continuous work in summer.
Germany imported laser: 12 laser bars handle, 10-40 million shots.
Big spot size 15x25mm,12*38mm,1200 w high power to sure fast hair removal.
Italian water pump: more better for the laser water ciculate
Painless and no side effect.



14 Years Laser Beauty Decvice Manuafactor

- High Feedback Top10 Supplier
- OEM & ODM SERVICE



我们拥有14年的激光美容设备制造经验，产品远销全球102个国家，拥有60000+客户，2年质保，14年工厂。我们提供OEM和ODM服务，是您值得信赖的合作伙伴。

Certificate display

Certificate is the best guarantee for you



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

CONTACT US



In terms of following trade details:

- 1)The shipping cost are based on DHL cost to your country
- 2)Delivery time:3-5 days after receiving payments.
- 3)Payment terms:T/T(bank transfer),Western Union.
- 4)Warranty:2 years for the whole machine
- 5)Warranty Policy:one month guarantee replacement (we bear all shipping cost),2years warranty,lifelong maintenance.
- 6)Packing method: Aluminum box with hard plastic foam.
- 7)Free-training to customers:Free We could offer DVD and User's manual and 10 Hours online service to our customers
- 8)Certifications:CE TUV SFDA ISO 13485
- 9)MOQ:1 UNIT
- 10)The quotation here above is valid within 1 month