

350g lightweight **handle**, more ergonomic

Available in **black or white**



755808 1064 1000 1000 1000000 10000 10000 10000

1000 1000 10 10 20 * 12 100000 1000.

.1000 1200 1000 12 10 35 * 12 1000000 1000
1000 1600 1000 16 10 35 * 12 1000000 1000.

1000 1000 100000 1000 10000

1000000 1000 10000000 10000000 1000000 1000 10000 1000000 1000 100000 1000



12*24mm 1200W handle
Additional therapeutic head



12*36mm 1800W handle
Additional therapeutic head



755808 1064 1064 1064 1064 1064 1064

1) 1064 1064 1064 1064 1064 1064

2) 1064 1064 1064 1064 1064 1064 1064 1064

1064 1064 1064 1064 1064 1064 1064 1064 (3.



0000 0000 0000 000 0 00000 000000 00000




00000 000000

1. 14 000000 000000 0 000000 0000000 0000 0000
 .0000000 000000 6 0 000000 000000 0 0000 / 000 .2

.3 .
 OEM /) ...)

The new 14-inch 4K screen

Support system customization



SHR 14寸 4K触摸屏

SHR	SHR 1064 808 755
SHR 16 - 8	SHR 16 - 8
SHR 100	SHR 100
SHR 14	SHR 14
SHR 808 1064 755 808	SHR 808 1064 755 808
SHR 12 * 35 20 * 12	SHR 12 * 35 20 * 12
SHR 808 4000000-10000000	SHR 808 4000000-10000000
SHR 10-150 2 / 150	SHR 10-150 2 / 150
SHR 40 ~ 800ms	SHR 40 ~ 800ms
SHR 1.0-10	SHR 1.0-10
SHR TEC	SHR TEC
SHR 800 1600 / 1200 / 1000 / 2000	SHR 800 1600 / 1200 / 1000 / 2000
SHR 220 60 / 110 50	SHR 220 60 / 110 50
SHR -10 ~ 3	SHR -10 ~ 3
SHR 27 ~ 31	SHR 27 ~ 31
SHR AC220V / 110V 50 ~ 60	SHR AC220V / 110V 50 ~ 60

□□□□□□□□ □□□□ □ □□□□□□□ □□□□□□ □□ □□□□□□