



# 12\*24mm or 12\*36mm handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...



- >>> Big 20\*12 □□□□□□ □□□mm, 12\*35mm for option
- >>> Laser technology, big power 10bar 1200W, 12 bar 1800W
- >>> 300g handle, light weight, free quick slide treatment



>>> New nose hair treatment head, applicable to small part treatment  
>>> 1 minute refrigeration frosting, painless treatment experience








**ALEX 755nm**  
**For white skin**  
(fine, golden hair removal )



**SPEED 810nm**  
**For yellow neutral skin**  
(brown hair removal)



**YAG 1064nm**  
**For black skin**  
(black hair removal)



## Treatment Effect

This is the clinical result of hair removal  
It takes 3--5 times to realize  
permanently hair removal









**15 Years**  
Laser Beauty Device  
**Manufacturer**

## Our Showroom



**OEM**           **ODM:**  
-



1. 生产流程 -  
 2. 生产流程 -  
 3. 生产流程 -  
 4. 生产流程 -

# Production Process



Warehouse spare parts



Parts assembly



Precision machining



Handle fabrication



Product assembly process



Quality inspection of finished products



Product packaging



Product packaging

1. 生产流程 -  
 2. 生产流程 -  
 3. 生产流程 -  
 4. 生产流程 -

24!