



1. 000000 0000 0 0000 00000000 000000.
2. 00000 000000 0000 000 0 000000 00 000000 00 00000000 .000000 0000 0 0000000000 0000000 000000.
3. 00000000 000000 000000 00000000 000000 00000 14 00000.
4. 000000 00000000 0 000000000 000000 0000 000000.5 .000000 000000 00000 0000 0 00 0000 000000 00 00000000 00000 000000000 00000000 00000000 0 0000 000000000!



>>Germany Emitter, strong energy

>>1200W power of hair removal on the whole body;

>>1-10Hz fast frequency

>> Italy water pump, it can keep machine working 24 hours without stop.



TEC

24 28 - 26

Working Principle

755nm and 808nm and 1064nm , suits for all skin and hair types.



ALEX 755nm

For white skin

(fine, golden hair removal)



SPEED 810nm

For yellow neutral skin

(brown hair removal)



YAG 1064nm

For black skin

(black hair removal)

□□□□ □□□□ 40-20 □□□□ □□ □□ □□□□□□

□□□□ □□□□ □□□□ □□□□□□ □□□□□□ □□□□□□ :□□□□□□ 808 □□□□

Alex 755nm: □□□□□□ □□□□□□ □□□□□□ □□□□ □□ □□□□ □□□□

□□□□ □□□□ □□□□ □□□□ □□□□ □□□□□□ □□□□□□ □□□□□□ □□□□ □□□□ □□□□ □□□□ :□□□□□□ 1064 □□□□□□ □□□□ □□□□□□ / nd yag / alexandrite

Machine Display



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,