



Stronger, Faster Two Handles




With 14-inch HD 4K Screen







□□□□□□ □□



□□□□□□ □□□




Laser show Handle laser bar optional



□□□□□□ □□□□

Working Principle Suits for all skin and hair types




- **755nm for white skin** (fine, golden hair removal)
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)



1. [unreadable] **15** [unreadable].
2. [unreadable].
3. [unreadable] TEC [unreadable].

Treatment Comparison



□□□□ OEM

1. □□□□□ □□□ □□□□
2. □□□□□□□ □□□□□□□ □□□ □□□□□ □□□□

customer visit



Packing

Safe and thoughtful packaging service



Tight packaging

The machine shall be made of waterproof materials and packaged

Anti collision foam board inside aluminum box



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service