



1. CE ISO13485
 2. CE ISO13485
 3. CE ISO13485
 4. CE ISO13485
 5. CE ISO13485
 6. CE ISO13485
 7. CE ISO13485
 8. CE ISO13485
 9. CE ISO13485
 10. CE ISO13485



1. CE ISO13485

2. CE ISO13485

1. .
 1000 :.2W 1200 W 20 * 12 mm 35 * 12 mm

3. 10-1 μs : 1000000 Hz . TEC μs 1200 μs : 12 TEC 4 μs $^{\circ}\text{C}$ 24 μs 1000 μs 1200 μs 1600 μs

One minute cooling -27°C

Best **TEC Cooling** system hair remover laser



1000 μs 1200 μs 1600 μs 20 * 1.12 μs 35 * 2.12 μs .3

350g lightweight **handle**, more ergonomic

Available in **black or white**




>>Germany Emitter, strong μs

1200<<W power of hair removal on the whole body;

>>1-10Hz fast

>> Italy water pump, it can keep machine working 24 hours without stop.




Hair removal principle

Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area



Natural hair loss, prevent regeneration, and achieve the purpose of hair removal



Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth

1. The laser beam is emitted from the handpiece and directed at the hair follicle.

2. The laser energy is absorbed by the melanin in the hair follicle.

3. The absorbed energy is converted into heat, which destroys the hair follicle and prevents regrowth.



1. 12.4

2. 6

3.

12.4

6

12inch 1200mm

40mm 40mm

Energy

Frequency

Frequency

Frequency

Frequency

Frequency

Frequency

Frequency

Frequency

12inch 1200mm

40mm 40mm

Energy

Frequency

Frequency

Frequency

Frequency

Frequency

Frequency

Frequency

Frequency

Frequency

Frequency

Frequency

Custom Section


CASE design



LOGO design



SYSTEM design



Frequency

OUR TEAM

There are more than 100 members of production team in our factory.





OUR COUNTRIES

All the products are taking with CE/ISO certification ,suitable for world market ,
mainly used on North America ,
South America Europe
60、000+ Customers Business development
in 102+ countries...

mingliangkj:

1. Weifang Mingliangkj Electronics Co. , Ltd (: MLKJ) 15

.2 r & d

-3.

PACKING

safe and thoughtful packaging service



Built-in prevention
collision bubble

Two- year warranty for machine
handle as consumable,
one-year warranty

Tight packaging

Training:
(video +manual+online service)
can keep you operate it easily



3-5 business days
delivery

professional guide:
24 hours professional online
customer service