



New Style Diode Laser

Painless, permanent hairremoval

24시간 운영. !!

Diode Laser

For You. For Life.



0000 0000000 00000 00000 000 1064 755808 0000

- 1) 0000 0000000 TEC 0 000 0 0000 24 0000 000 00000000 0000 000000 00 00 0000 0 0000 000000 000000 000000 .000000 00
- 0000 0000 40.000.000 0 00000000 00 0000000000 0000000 000000 00000 00000000 (2
- .000000000 000000 00000 00000 0 00000000 00000000 00000 00000 0 00000000 (3
- 000000 00000000 0000 0000000 0000 00000000 0 00000 00000 0 0000 1600 000000 00000 0000 (4.

350g lightweight **handle**, more ergonomic

Available in **black or white**



755808 1064 1000 10 20 * 12 1200 12 35 * 12 1600 16 35 * 12

1000 10 20 * 12 1200 12 35 * 12 1600 16 35 * 12

1200 12 35 * 12 1600 16 35 * 12

1600 16 35 * 12

1000 10 20 * 12 1200 12 35 * 12 1600 16 35 * 12

1000 10 20 * 12 1200 12 35 * 12 1600 16 35 * 12



12*24mm 1200W handle
Additional therapeutic head



12*36mm 1800W handle
Additional therapeutic head



755808 1064 1064nm 1064nm 1064nm 1064nm 1064nm

- 1) 1064nm 1064nm 1064nm 1064nm 1064nm
 - 2) 1064nm 1064nm 1064nm 1064nm 1064nm 1064nm 1064nm 1064nm
- 1064nm 1064nm 1064nm 1064nm 1064nm 1064nm 1064nm 1064nm (3.



[腋下脱毛](#)
[上唇脱毛](#)
[下巴脱毛](#)
[背部脱毛](#)




1. 14

2. 6

.3. OEM (/) ...)

The new 14-inch 4K screen

Support system customization



Technical specifications

Model	1064nm 808nm 755nm
Power	16 - 8W
Spot size	100mm²
Wavelength	14nm
Frequency	808nm 1064nm 755nm 808nm
Spot size	12 * 35mm² 20 * 12mm²
Power	808nm 40000-100000W
Frequency	10-150Hz (2Hz / 150Hz) (2Hz / 150Hz)
Spot size	40 ~ 800ms
Wavelength	1.0-10nm
Power	TEC TEC TEC TEC
Power	800nm 1600 / 1200 / 1000 / 2000
Power	220nm 60 / 110nm 50 / 100nm
Power	-10 ~ 3nm
Power	27 ~ 31nm
Power	AC220V / 110V 50 ~ 60Hz

□□□□□□□□ □□□□ □ □□□□□□□ □□□□□□ □□ □□□□□□