



□□□□□□ □□□□



□□□□ □□□□ □□□□ □□□□

□□□ 600 □□□□□ 5 □ □□ 14 \* 14 □□□□□□ □□□□

## Handle Display

*The handle is small and light, weighing as low as 168.8g.  
Very light to operate*

[illegible]

# Cooling Effect

*The handle has a cooling effect that improve treatment comfort.*



**Just One minute!**

Quick cooling down to

**-25°C**

## Working Principle

755nm and 808nm and 1064nm , suits for all skin and hair types.



**ALEX 755nm**

**For white skin**

(fine, golden hair removal )



**SPEED 810nm**

**For yellow neutral skin**

(brown hair removal)



**YAG 1064nm**

**For black skin**

(black hair removal)



# 6<sup>+</sup> ADVANTAGE

HANDLE OF 808 DIODE LASER DEVICE



No pain



No side  
effect



Germany  
imported bar



Big spot  
15\*25mm



super cooling  
system



Permanent  
hair removal



# Before and After


Treatment comparison



# Screen Display

13.3 inch 4K true color touch screen

The display screen is clear at a glance and easy to operate



6 language for your choice. Super cool touch Experience .

Special language can be added according to your actual requirements.

Your logo also can be added on diode laser screen.

1. 13.3 英寸触摸屏 4K 真彩色触摸屏
2. 触摸屏分辨率 6 英寸触摸屏分辨率 1920 / 1080
3. 触摸屏支持多点触控操作
4. OEM 定制 / 定制) 触摸屏...

# We have OEM Services

Serving your needs

Language  
System  
program



Screen/Machine  
LOGO

Colors



Appearance



Other  
customization







Product Customization Design



Production and Processing



Program Debugging



Machine Debugging



Batch Production



Fine and Safe Packaging

□□□□□□ □□□□□□



# Packing

safe and thoughtful packaging service



## Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,  
one-year warranty

**OEM&ODM service for distributor.**

## Tight packaging

Training: (Video+Manual+Online Service)

Can Keep You Operate It Easily



## 3-5 business days delivery

Professional guide:

24 Hours Professional online customer service