



- . . . . .
- . . . . . \*
- . . . . . \*
- . . . . . \*
- . . . . . \*
- . . . . . 1064 808 755 □ . . . . . 808 . . . . . \*

**350g**  
Ultra light handle




12×36mm  
**Handle**  
1800W diode laser hair removal



12×24 mm  
**Handle**  
1200W diode laser hair removal

Three Waves 755nm 808nm 1064nm 0 000000 000000 00000 0000 00000 000 000000.

755 .000000 000000 (0000000 / 0000000 000000) 00000000 0000000 00000000  
.(00000000) 0000000 000000 0000 00000000 00000000 808  
1064nm 000000 00000000 (00000000 0000000) 000000000 00000000.






**ALEX 755nm**  
**For white skin**  
(fine, golden hair removal )



**SPEED 810nm**  
**For yellow neutral skin**  
(brown hair removal)



**YAG 1064nm**  
**For black skin**  
(black hair removal)



## Treatment Comparison





Emergency stop button

12 inch big screen quick touch easy operate

Diode laser handle

Vents

Plug

1. 15.6 inch touch screen

1. 15.6 inch touch screen
2. 12 inch big screen quick touch easy operate
3. Diode laser handle
4. Emergency stop button
5. Vents
6. Plug

1. 15.6 inch touch screen