



-
- *
- *
- *
- *
- *
- *




ALEX 755nm
For white skin
 (fine, golden hair removal)




SPEED 810nm
For yellow neutral skin
 (brown hair removal)



YAG 1064nm
For black skin
 (black hair removal)



Treatment Comparison





Emergency stop button

12 inch big screen quick touch easy operate

Diode laser handle

Vents

Plug

□□□□□□ □□ □□□□ □□□□ □ □□□□□ □□□□□□ □□□□□□ □□□ □□□□□ □□□ □□□□