




TEC 24



1 minute
and you're done

35mm {

FASTER

□□□□□□ □□□□



1. 14 .
 .
 .
 .4 OEM

16 12 10 8	808nm 1064nm / 808nm
0-150 2	1-10
40-800	LCD 14.0 TFT True Color LCD
4000	220 60 / 110 50 /
NW / GW	62 78 /

**Standardized
production**



**Professional
Production R & D
Sales Department**



**Mass production
of various styles**



- >>OEM your own machine body.
- >>OEM your own program software.
- >>OEM pretty machine colors.
- >>Print your LOGO on machine body and screen.

Custom Section


CASE design



LOGO design



SYSTEM design



CERTIFICATE DISPLAY

