

□□□□

*.3 □□□□□ □□□□ □□□ □□□□□□ □□□ 1 □ 3 □ □□□□□□ 755 □□□□□□ 808 □□□□□□ 1064 □□□□□ □□□□□□□ □□□ 1600 / □□□ 1200 / □□□ 1000 □□□□ □□□□ :□□□□□ □□□

*. □□□□□□ □□□□□ □□□ □□□□□□ □□□□□ □ □□ 35 * 12 □ □□ 20 * 12 □□□□ □□□□□□ □□□□□□!

. □□□ □□ □□□□ □□□□□ □□□□ :□□□□□□□ □□□□ Dual- TEC □ □□□ □□□□□ □□□□□□ □□□ □□□□ □□□□□ 40 :□□□□□ □□□.. □□□□□ □□□ □□□□ □□□□ 24 □ □ □□□□□ □□□□ □□□□□□□□

* □□□□ □□□□ □□□□□ □□□□.

* □□□ 40000000 □□□□□□□ □□□□□□□□□ □□□□□□□ □□ □□□□□□□ □□ □□□□□□□ □□□□□□ □□□□□ □□□□□.


*. □□□□ □ □□□□ □□□□ □□□□□ □□□

*. □□□□□□ □□□□□□ □□□□□□ □□□□□ □□□□□□

* 14.0 □□□□□□ □□□□□ 6 □□ □□□□□□ □□□□ □□□□□ □□□□ □□□□.

What is diode laser hair removal?


Alma soprano xl titanium Diode laser hair removal comes with 808nm wavelength laser stack or 755+808+1064 triple wavelength laser stack with semiconductors technology. They are assembled together to produce light for permanent hair removal/hair reduction/depilation/epilation treatment!



Emit a laser beam



The laser beam is absorbed by hair follicle melanin




Different color hair has different ability to absorb light wave



After absorption, the laser energy will be converted into heat energy



Hair follicles and surrounding stem cells lose their activity and fall off



So reach hair removal effect



755 808 1064nm 光波照射器 照射器 照射器.
照射器 照射 照射 照射器 照射 照射 照射器 照射器 照射器:
755 照射 照射 照射) 照射器 照射器 照射器)
808 照射器 照射 / 照射器 照射器 照射器
1064nm 照射 照射) 照射器)

Treatment effect

Suit to any color of skin



Before&After



このように、肌の色や肌の状態によって、効果は異なります。また、肌の色や肌の状態によって、効果は異なります。また、肌の色や肌の状態によって、効果は異なります。

BEFORE AND AFTER TREATMENT

MAKE YOUR SKIN SILKY AND FULL OF CHARM!

