



0000 00000000 000000 000 00000000 000000 000000 000000 000000 000
 0000 0000 0000 0000 **1064 755808** 00000000 **ipl** 00000000 000000 000000




15 / 10

15 / 10

3

755



00000000 000

Mini Portable

The net weight of the handle is
about equal to one iphone

285g

Ergonomic handle
It's not tiring to take off



产品特点 特点

重量 1800 / 重量 1200 重量 重量

36 * 12 24 * 12 重量 重量

* 285 重量 重量 重量 重量 重量 重量 重量 重量 重量 重量


* 重量 重量 (重量 重量 重量) 重量 重量 重量 重量 重量 重量 重量

EXFU

Exfu Violin

One-of-a-kind styling
Build your own hair removal machine

One minute cooling, 12x24cm²super cool area.
Newest design handle 0.31kg





800/1000/1200/1600W

50 Million Shots

USA / Germany Imported Laser Bar

755nm+808nm+1064nm



ALEX 755nm
For white skin
(fine, golden hair removal)






SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)

755 808 1064 755nm 808nm 1064nm 755nm 808nm 1064nm 755nm 808nm 1064nm 755nm 808nm 1064nm 755nm 808nm 1064nm



Ingenious details I am better than others

Product detail
layout



Surround light strip

Cool lighting effect
not dazzling



Newest design handle 0.31kg

One minute cooling
Customizable glowing logo



One-of-a-kind styling

Ingenious production
focus on details



電源電圧	電源電圧 電源電圧
電源電圧 電源電圧	1200 ---- 電源 800 電源 12 ---- 8 電源 電源電源電源 電源電源電源電源 電源電源電源 電源電源電源 / 電源電源電源
電源	14 4 電源K 電源電源 電源電源 電源電源
電源電源 電源電源	808nm 755 電源nm 808nm 1064nm
電源電源	50 電源電源 電源電源
電源電源	10 ~ 150 電源電源電源 電源電源 電源 2 電源 / 電源
電源電源	1-10 電源電源
電源電源	電源電源電源 電源電源電源 電源電源 TEC 電源 電源電源電源 電源電源電源 電源電源電源 電源電源 電源電源 電源電源 電源電源電源 電源電源電源 電源電源電源 電源電源電源 電源電源電源 電源電源電源
電源	3500 電源
電源電源電源 電源	12 * 24 電源電源電源電源 電源 36 * 12 電源 電源
電源電源電源電源 電源電源	110 電源電源電源電源 電源電源 50 / 電源電源 220 電源 電源電源 60 / 電源電源
電源電源電源 電源電源	35 電源
電源電源電源電源 電源電源	45 電源

7 * !電源電源電源電源 電源電源 電源電源 24 電源電源
電源電源電源電源 電源 電源電源 電源電源電源!