

Why

choose us?

14 years factory

14 years of focus on the development of beauty equipment, the pursuit of higher product quality, making beauty entrepreneurship easier


60000+ customers in 102 countries

The products are sold to 102 countries, serving more than 60,000+ customers

2 years warranty

2 years warranty for each machine All question will be response within 24 hours solved within 72 hours

Make Your Beauty Business More Easier !



00000000

14 0000 0 000000 00 000000 00 000000 A.ODM / OEM B. 000 000000 00000000 00000000 00000 00000 00000000 0000 00 0000 0 000000 C. 000000 0000 0000 CE 0 ISO 13485 0 000000 000000 20 00 00000 000000 D. 000000 0000000 00000000 0000000 000000 000000 000000

00000000 0000

DIODE LASER

*3 waves 1064nm +808nm + 755nm,
*Safe, Fast, Painless, permanent
*For all skin and hair style hair removal

>>>

1. 0000 0000 000000 000000.
- 2-0000 000 40.000.000 000000 0000000000 00000000 00000000 00 00000000 00 00000000 0000000 000000.
- 3.000000 0 000000 0000 00000000 00000
4. 000000 000000 000000 00000000 000000 0000000

5.14.0 000000 000000 6 00 000000000 0000000000 0000000 00000 00000.

Machine display

Show the machine from three angles, looking at the machine comprehensively.



MACHINE DETAILS DISPLAY


EXQUISITE DETAIL DISPLAY



00000 000

測試時間	20-40 分鐘 測試時間
測試次數	10 ~ 150 測試次數 測試時間 2 分鐘 / 次
測試對象	1-10 人
測試地點	室內 室內 室內
測試時間	3500 分鐘
測試時間 測試	12 * 20 測試時間 測試 35 * 12 分鐘 測試
測試時間 測試	110 測試時間 測試 50 / 測試 220 分鐘 測試 60 / 測試
測試時間 測試	95 分鐘
測試時間 測試	53 * 40 * 105 分鐘

測試 測試



測試 測試

1. 測試 測試 6 分鐘 測試 6 分鐘 測試 14 分鐘 測試 測試
2. 測試 測試 測試 14 分鐘 測試 測試
3. 測試 測試 測試 6 分鐘 測試 測試 OEM 測試) 測試
4. 測試 測試 測試 測試 測試 測試 6 分鐘 測試 測試

測試 測試 測試 測試 測試 測試

