



□□□□□□□□ □□□





EXFU IPL LASER : 50 * 15 CM

* EXFU IPL LASER 50 * 15 CM . 30000 CM 150000 CM HD LCD . 15.6 CM . EXFU IPL LASER 50 * 15 CM . 30000 CM 150000 CM HD LCD . 15.6 CM . EXFU IPL LASER 50 * 15 CM . 30000 CM 150000 CM HD LCD . 15.6 CM .

* EXFU IPL LASER 50 * 15 CM . 30000 CM 150000 CM HD LCD . 15.6 CM .



Multi-angle display



Non-cooling effect



Cooling effect

Specification

- High-quality IPL handpiece with super cooling system
- Optional Spot Size 15*50mm, 15*35mm, 12*30mm
- Long shots time:
IPL: 150,000 times
- 7 filters: 420/510/560/585/640/690/755nm
Standard: 420/510/560/690nm

Cooling Effect

The handle adopts a refrigeration effect which can effectively cool the skin in the treatment process and improve the comfort of treatments.

large
area

Cool
painless
comfortable


Protect
surrounding
skin

Fast
hair
removal

Filters for choice



ABS plastic filter box,
more exquisite, more durable

						
420nm	510nm	560nm	585nm	640nm	690nm	755nm
Acne removal Vascular treatment	Freckles removal	Skin rejuvenation wrinkle removal	Removal of visible blood vessels	Hair removal (fair skin)	Hair removal (medium skin tone)	Hair removal (darker skin)

Standard configuration: 420nm 510nm 560nm 690nm

Before and after



Skin rejuvenation



Freckle removal



wrinkle reduction



Acne clearance



Hair removal




Pigmentation treatment

1. 15.6 英寸显示屏
 2. 6 英寸触摸屏 / 摄像头
 3. 内置摄像头
 4. OEM 摄像头 / 摄像头...

Suitable for any complexion

The elight handle is equipped with **seven filters**, which can be used for **different treatments** and **different skin colors** to select the corresponding filters, thus making the operation more convenient.



! 24 小时 全天候 服务 热线 021-51000000
 官方网站: www.elight.com.cn