



HIGH POWER DIODE LASER

755+808+1064nm
For all skin and hair types

Newest!

[Learn more details](#)

□□□□

.□□□ 16——8 □□□□□□ □□ □□□□□□□□ □□□□□□ □□ □□□□□ □□□ □□□□ *
.□□□□□□ □□□□□□ □□□□ □□ □□□□□ □□ □□□□□ □□□□□ □□□□□ □□□□□ 50 □□ □□□□ *
□□□□□□ □□□□□ □□□□ □□□□□ □□□□□ □□□□□ □□□□□ □□□□□ □□□□□ □□□□□ □□□□□ 3 *





Arm hair removal

Lip hair removal

Face hair removal

Leg hair removal

Back hair removal

Underarm hair removal

Bikini hair removal

DIODE LASER

755/808/1064nm diode laser, for all type skin hair removal, painless



ADVANTAGE

- **PAINLESS:**755/808/1064nm diode laser for all type skin hair removal
- **FASTER:**Large area spot sliding operation
- **NO TRAUMA:**There is no trauma to skin tissue
- **SAFETY:**To avoid the light of the deputy to reduce the difficulty of operation



□□□□□□ □□□

1200 □□□□ □□□□□□□□ □□□□□ □□□ □□□ 1800 □ □□□

□□□□□□ □□□ □□□ 35 * 12 □□ 20 * 12

350 *

() *

800/1000/1200/1600W
50 Million Shots
 USA / Germany Imported Laser Bar

755nm+808nm+1064nm



ALEX 755nm
For white skin
 (fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
 (brown hair removal)



YAG 1064nm
For black skin
 (black hair removal)

• *Cooling effect* •

The handle is frosted for one minute,
making your treatment more comfortable and painless



Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.





✓ 14 Android Screen

1. Three wavelength diode laser.
2. Golden laser bars from German or USA improved, 40,000,000+ longer lifespan.
3. Safe, Fast, Painless, permanent
4. For all skin and hair style hair removal
5. 14.0 inch true color touch screen with 6 skin colors.



808 30	808 30
800 16 ---- 8	800 16 ---- 8
1600 ----	1600 ----
14 4	14 4
808nm 755 nm 808nm 1064nm	808nm 755 nm 808nm 1064nm
50	50
10 ~ 150	10 ~ 150
2	2
1-10	1-10
TEC	TEC
3500	3500
12 * 20	12 * 20
35 * 12	35 * 12
110	110
50 / 220	50 / 220
60 /	60 /
95	95
105	105

!000 0000000 0000 0 0000000 000 00000000 00 000000
00000000 000 0000 **24 !!**