

Diode Laser



15 Bar **1800W** Handle

*Increase the treatment head of nasal hair
and treat small parts easily



.0000 000000 00000 00000 000

.000000 00000 00 000 000 00000 .0000 00 *

.000000 00000 00 000 000 00000 *

.00000 000 *

0 00000 000000 000000 00000000 *

0 0000000 1064 808 755 00 0000000 808 000000 000000 000000 000000 *

Ultra light handle



12×36mm

Handle

1800W diode laser hair removal




12x24 mm

Handle

1200W diode laser hair removal

755 .000000 000000 (000000 / 000000 000000) 0000000 000000 0000000
 .(0000000) 000000 000000 000 000000 0000000 808
 1064nm 000000 0000000 (000000 000000) 00000000 0000000.






ALEX 755nm
For white skin
 (fine, golden hair removal)




SPEED 810nm
For yellow neutral skin
 (brown hair removal)



YAG 1064nm
For black skin
 (black hair removal)



Treatment Comparison





Emergency
stop button

12 inch big screen
quick touch
easy operate

Diode laser handle

Vents

Plug