

SAFE AND PAINLESS

# DIODE LASER HAIR REMOVAL MACHINE

LEARN MORE



MLKJ's ICE! .

# 15 Years Laser Beauty Decvise Manuafactor

• High Feedback  
Top10 Supplier

• OEM & ODM  
SERVICE



# • *Cooling effect* •


The handle is frosted for one minute,  
making your treatment more comfortable and painless



Suitable for hair removal on any part of the body,  
Such as arms, legs, face, armpits, back, chest, etc.




- \* 1800
- \* ...
- \* ...
- \* ...



755 nm for white skin (fine, golden hair removal );



808 nm for yellow neutral skin (brown hair removal);



1064 nm for black skin (black hair removal)

### □□□□□□ □□□

1. □□□□□□ □□□□□□□□ □□ □□□□□□ □□ □□□□□□ □□□□□□ □□□□□□-2 .□□□□ □□□□ □□□□□ □□□□□□
- 3 .□□□□ □□□ 40.000.000 □□□□□□ □□□□□□□□□□.Safe □ □□□□□ □□□□□□ .4 □□□□ □ □□□□ □□□ □ □□□□□ □□□□□□ □□□□□□ 6 □□ □□□□□□□□ □□□□□□□□ □□□□□□ □□□□ □□□□ □□□□□ □□□□□□ □□□□□□□□□□□□.





# For all skin types

Triple wavelength laser work together

755  
nm

808  
nm

1064  
nm

755nm/808nm/1064nm

755nm  
808nm  
1064nm

## Laser hair removal treatment theory



Hair active growth phase(3-6years)



laser treatment



Transition phase (1-2weeks)



Resting phase (1-2 weeks)



Return to growth phase

□□□□□	808 29 □□□□
□□□□□□ □□□	808 □□□□□□ □□□□□ 3 □□□□□□□□ 755/808/1064 □□ □□□□ □□□□□□□□
□□□	14 4 □□□□K □□□□□□ □□□□ □□□□
□□□□□□ □□□□□	755/808/1064
□□□□□□	20-40 □□□□ □□□□□□
□□□□□	10 ~ 150 □□□□□□□□ □□□□ □ 2 □□ / □
□□□□□□	1-10 □□□□□
□□□□□□	□□□ □□□□ □□□□□□□□
□□□□	3500 □□□□
□□□□□□□ □□□	12 * 24 □□□□□□□□□ □□ 36 * 12 □□ □□
□□□□□□□□□ □□□□□	110 □□□□□□□□ □□□□ 50 / □□□□□ 220 □□ □□□□□ 60 / □□□□□
□□□□□□□ □□□□□	95 □□□□
□□□□□□□□□ □□□□□	105 □□□□
□□□□□□ □□□	53 * 40 * 105 □□

□□□□ □□□

125 \* 56 \* 70.4



□□□□□ □□□□□ □□□□ □□□□ □□□□□ □□□ □□□□ □ □□□ □□□□ □□□□□ □□□□□  
 □□□□□!

□□□□□ □□□□ □□□

□□□□□ □□□□

\* □□□□ 14.0 □□□□

\* □□□□□□ □□□□□ □□□□

\* □□□□□□□□ □□□□□□□ □□□□□□ □□□□□□ - □□□□□□□ □□□□□

\* □□□□□□ □□□□□□ □□□□□ □□□□□ □□□□

# Custom Section

LOGO design



SYSTEM design



□□□□ □□□  
□□□□□□□□□□ □□□□□ □□□□□□□ □□□□□ □□□□ □□□□□ □□□□□





# Our customers

60000+ CUSTOMERS



102

Countries

OEM/ODM

Customize the machine according to customer needs

## CERTIFICATE



14 我们拥有 14 项国际专利，覆盖全球 140 多个国家和地区！

13 我们拥有 13 项国际专利，覆盖全球 130 多个国家和地区！

我们拥有 CE 认证，符合欧盟 CE 标准，TUV 认证，符合

国际安全标准，符合 ISO 9001 质量管理体系，符合 ISO 13485 医疗器械

质量管理体系！

我们拥有 14 项国际专利，覆盖全球 140 多个国家和地区，符合 ISO 9001 质量管理体系，符合 ISO 13485 医疗器械

质量管理体系！

# Packing

safe and thoughtful packaging service



## Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,  
one-year warranty.

**OEM&ODM service for distributor.**

## Tight packaging

Training: (Video+Manual+Online Service)  
Can Keep You Operate It Easily.



## 3-5 business days delivery

Professional guide:

24 Hours Professional online customer service,