



DIODE LASER HAIR REMOVAL MACHINE

- SUPER ICE PAINLESS EXPERIENCE
- PERMANENT HAIR REMOVAL
- COMFORTABLE HAIR REMOVAL

1min} Fast and painless hair removal
One minute cooling -21°C



Large Spot Size

Quick and Comfortable

With large spot size of 1.2*3.5cm², for faster treatments and better patient experience.



TEC Plus

Continuous Contact Cooling

TEC is an advanced technology that continuously cools skin and facilitates range-controlled temperature throughout the entire treatment. Patients can now enjoy a completely pain-free, cool and comfortable experience throughout the session.

□□□□

* □□□□ □□□□ 40 □□□ □□□□□ □□□ □□□□ □□□□
□□□□ □□□□ □□□□□ □□□ 1600 □□□□ 16 □ □□□ 1200 □□□□ 12 □ □□□ 1000 □□□□ 10 *
□□□□□□ □□ 38 * 12 □ □□ 25 * 15 □ □□ 20 * 12 □□□□□□ □□□□ *
□□□□□□□ □□□□ □□□□ □□□□ □ □□□□□ □□□□ □ □□□□ 450 □□□□□ *
□□□□□ □□□□□□ □ (□□□□□□□ □□□□□□ □□□□) □□□□□ □□□□□ □ □□□□□ □□□ □□□ *

Handle Details


Three Wavelengths Work Together





12*20nm


755nm Laser
808nm Laser
1064nm Laser





12*35nm

755nm Laser
808nm Laser
1064nm Laser




□□□□□ □□□□□ □□□□ □□□ □□□ □□□□□□□□□□

Alex 755nm □□□□□□□ □□□□□□□
□□□□□□□ □□□□□ □□□□□□□ 808 □□□□ □□□□
□□□□□□□ □□□□□ □□□□□□□ 1064 □□□□□ □□□□□

Working Principle

Triple wavelength laser work together

Suits for all skin and hair types



- **755nm for white skin** (fine, golden hair removal)
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)

□□□□□□ □□□□□

