



*IPL A6*  
 For hair removal  
 & skin rejuvenation

1. 50 \* 15 cm, 30000-150000 pulses, 8.4" LCD TFT, IPL handle, emergency switch, key switch, power cord, etc.  
 2. 8.4" LCD TFT, IPL handle, emergency switch, key switch, power cord, etc.  
 3. IPL handle, emergency switch, key switch, power cord, etc.



000000 000

# Elight Handle Design



## Specification

**Optional Spot Size:**  
15\*50mm

**Imported UK lamp**

**Long shots time:**  
150,000--300,000 times

**7filters:**  
420/510/560/585/640/690/755nm

**Super cooling system**



□□□□□□ □□□□ □□□□□ □□□□□ □□□□□ □□□□ □□□□ □□□□.



□□□□ □□□ □□□□□ □□□□ **8.4** □□□□ □□□□□ □□□ □□□□ □□□□

1. 8.4 □□□□□ □□□□□ □ □□□□□ □□□□ □□□□ □□□□ □□□□

- .2 . /
- .3 .
- .4 OEM ( / )...

# Screen interfac

## Professional Screen, Easy operation



**Main Menu**  
8.4 inch true color big touch screen  
Super cool touch Experience.



**IPL mode:**  
5 options for skin treatment




**IPL mode:**  
operation interface



**Multi-language screen:**  
6 languages for your choice



**System setting**



**System setting**

□□□□ □□ □□□□□□

□□□□□

□□□□□□ □□□□□

□□□□

□□□□

□□□□□□□ □□□□

□□□□

□□□□□

□□□

□□□□

□□□□□□□

IPL: 15 \* 50 □□□□□□ □□□□□□ □□□□ □□□□

420/510/560/585/640/690/755 □□□□□□□□

150.000 □□□□ 30.000 □□□□

□□□□ 8.4 □□□□□□ □□□□ □□□□□ □□□□

1200 □□□□ TEC Cooling Air Cooling Water Cooling 3 in 1 system

2 □□□□□ □□□

□□□□ 220 □ □□□□ 110 □ □□□□□□□ □□□□□□□ □ □□□□□□□ □ □□□□□□□ □ □□□□□□□ □□□□□□□□

30 □□□

□□□□□□ □□□□□□ □□□

□□□□ □□□□ □□□ □□

## Multi-angle display



Left view



Front view



right elevation