




000000 000



000000 000






Laser show Handle laser bar optional



④ 10bar

④ 12bar

④ 16bar



□□□□□□ □□□□

Suits for all skin and hair types



808nm

1064nm



- **755nm for white skin** (fine, golden hair removal)

● **808nm for yellow neutral skin** (brown hair removal)

- **1064nm for black skin** (black hair removal)




- 1.** □□□□□□ □□□□□□ □□□□ □□□□ □□ □□□□□□ □□ □□□□□□ **15** □□ □□□□ □□□□□□ .□□□□□□.

2. 0000 000 0 00000000 0000000 000000 000 0000000 00000 00000 00 .0000000.

[illegible]

Treatment Comparison



00000 OEM

1. 000000 0000 0000
2. 00000000 00000000 000 000000 00000

customer visit



Packing

Safe and thoughtful packaging service



Tight packaging

The machine shall be made of waterproof materials and packaged

**Anti collision foam board
inside aluminum box**



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service