



Laser luxe

Powerful

fastly

Safety

10) 波長 ≤ 1064 nm : 皮膚深部に到達し、 10^{-6} 秒パルス

照射する。照射深さ 0.5-1.0mm

特徴:

■ 皮膚深部を加熱し、真皮層に刺激を与え、コラーゲン産生を促進し、皮膚の弾力性を向上させる。

■ 皮膚の水分量を高め、保湿効果がある。

■ 皮膚の温度を上げ、血流を促進し、Q-switching

Product advantage

- ⬆️ Fast and scar-less
- ⬆️ imported 7 joint articulated arm 360 treatment without dead angle and ensure the highest energy output minimum energy loss during laser transmission.
- ⬆️ Spots no longer appear
- ⬆️ 2-10mm adjustable spot size Different treatment areas are applicable Energy density is automatically adjusted with spot size.
- ⬆️ The combination different laser pulse durations ,Provide an optimal method for shattering all sizes of pigment particles.

000000 000000

000000 0000 00000000 00000000 00000000 00000000 00000000 00000000 00000000 00000000 :00000000 00000000 .1 :00000000
 0000 00 00000 000000000 00000000 00000000 00000000 :00000000 .2 .000000 00000 0000000 0000000
 0000 0000 00000 00000000 00000 :00000000 000000 .3 .00000000 00000000 000 00 00000 000 00000000 00000 00000000
 00000000 000000 000000 000000 00000 000 00 000 0000000000 0000000000 0000000000 00 00000000 00000000
 00000000 00000 00000 000000 000000 00000 00000 :000000 0000 .4 .0000 0000 0000 0000000000 00000000 0000000000
 0000000000 00000 00000 00000000000 0000000000 00 00000 000000000 00000000 00000000 00000 00000 000000000
 00000 000000 :000000 00000000 .5 .00000000 00000000 Ruby Laser 00000000 0000000000 00000 000000 000000 00000 0000
 00000000 00000000 00000000.

TECHNICAL PRINCIPLE



Traditional laser

Traditional nanosecond lasers predominately rely on photothermal action, delivering heat to the pigment and surrounding tissue



Laser luxe

Laser luxe takes advantage of Pressure Wave Technology to shatter the target ink into tiny particles that are easily

Q-switched Nd Yag laser is a type of laser that is used for various medical and cosmetic purposes. It is a pulsed laser that emits light at three different wavelengths: 1064nm, 755nm, and 532nm. The 1064nm wavelength is used for treating dark pigmentation, such as freckles and age spots. The 755nm wavelength is used for treating red pigmentation, such as broken capillaries and rosacea. The 532nm wavelength is used for treating vascular lesions, such as spider veins and hemangiomas. Q-switched Nd Yag laser is also used for tattoo removal and skin resurfacing.

Before & After



Parameters Table

Device Name	Laser luxe
Wavelength	1064nm 755nm 532nm
Screen Size	12 inch 4K Style touch screen
Pulse Duration	~7ns@1064nm ~6.5ns@532nm
Frequency	1-10hz
Spot size	2-10mm adjustable
Energy	1064/1000mj 755/1000mj 532/1000mj
Beam of light transmission	7 articular-arm of light guide transmitting
Indicator of aiming light	650 red diode laser
Cooling	Water cooling+Air cooling
Voltage	AC220V/110V 50HZ/60HZ
Demension of machine	93.6*92.7*39cm
Package	Aluminum box
Warranty	2 years



Q-switched Nd Yag laser is a type of laser that is used for various medical and cosmetic purposes. It is a pulsed laser that emits light at three different wavelengths: 1064nm, 755nm, and 532nm. The 1064nm wavelength is used for treating dark pigmentation, such as freckles and age spots. The 755nm wavelength is used for treating red pigmentation, such as broken capillaries and rosacea. The 532nm wavelength is used for treating vascular lesions, such as spider veins and hemangiomas. Q-switched Nd Yag laser is also used for tattoo removal and skin resurfacing.

Q-switched Nd Yag laser is a type of laser that is used for various medical and cosmetic purposes. It is a pulsed laser that emits light at three different wavelengths: 1064nm, 755nm, and 532nm. The 1064nm wavelength is used for treating dark pigmentation, such as freckles and age spots. The 755nm wavelength is used for treating red pigmentation, such as broken capillaries and rosacea. The 532nm wavelength is used for treating vascular lesions, such as spider veins and hemangiomas. Q-switched Nd Yag laser is also used for tattoo removal and skin resurfacing.





You'll get

Six value-added services

One-stop after-sales solution



2 years machine warranty
1 year for handle



Free enterprise training



Test **videos** and **pictures** about the machine



A professional **training service**
training files
training videos



Customized logos, posters and promotional videos, put the logo on screen system



Parcel **tracking service**
Help to do Customs clearance

服務內容 詳情 請 洽：

* 服務內容 詳情 請 洽 代理商 或 服務 熱線 400 888 8888 或 訪問 我們 的 網站 www.mlcj.com 查詢 詳情。

* 本 項 服務 僅 限 於 中國 內地 地區 客戶 使用 且 僅 限 於 辦公 時間 內 提供 服務 詳情 請 洽 代理商 或 服務 熱線 400 888 8888。

* 本 項 服務 僅 限 於 中國 內地 地區 客戶 使用 且 僅 限 於 辦公 時間 內 提供 服務 詳情 請 洽 代理商 或 服務 熱線 400 888 8888。

! 我們 提供 24 小時 緊急 維修 服務 詳情 請 洽 代理商 或 服務 熱線 400 888 8888 或 訪問 我們 的 網站 www.mlcj.com 查詢 詳情。