

OEM / ODM  
 10000 100 10 1000 10

# Build more trusted partners

## Our customers

60000+ CUSTOMERS

## OEM/ODM

Customize the machine according to customer needs



## CERTIFICATE

Obtained multi-way authoritative certification,  
 product testing certification, product patent authority,



10000

\* 1000000 100 1000000000 100000000 100000000 Dilas .1000000 10000 1000000000

.10000 10000 100000 1000 100000 100 100000 3 100 10000 10 10000 100000 40 100 10000 \*

808 \*nm 1000000 1000000 10000 100000000 10000

100000000 1000 1800 / 1000 1200 10000 10000 :100000 1000 \*

!10000000 1000000 1000 10000000 1000000 100 36 \* 12 100 100 24 \* 12 100000 1000000 10000 1000 \*

1000 100 10000 100000 10000 :10000000 10000 \* Dual- TEC 10 100000 10000 1000000000 1000 100000 10000000 1000000 1000

.10000 1000 10000 10000 24 10 10

10000 100000 40 :100000 1000 \*

10000000 1000

# 12\*24mm or 12\*36mm handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...



1200 36 \* 12 24 \* 12 350 1800

\* TEC (Thermoelectric Cooling) system



\* TEC (Thermoelectric Cooling) system

\* 100% 100% 100% 100% 100%  
 \* 100% 100% 100% 100% 100% 100% 100% 100%  
 100% 100%

**Hair removal comparison** The real picture taken by the customer  
 Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

**Hair removal comparison** The real picture taken by the customer  
 Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

- 100% 100%  
 100% 100% 100% 100% 100% 14 .1  
 100% 100% 100% 100% 100% 100% 6 100% 100% 6 100% 100% .2  
 100% 100% 100% 100% 100% 6 .3  
 100% 100% .4 OEM 100% / 100% 100%...)  
**5.OEM / ODM** 100%  
 >>OEM your own machine body  
 >>OEM your own program software  
 >>OEM pretty machine colors  
 >>Print your LOGO on machine body and screen  
 >>R & D team and Quality inspection Show



# Packing

safe and thoughtful packaging service



## Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,  
one-year warranty.

**OEM&ODM service for distributor.**

## Tight packaging

Training: (Video+Manual+Online Service)  
Can Keep You Operate It Easily.



## 3-5 business days delivery

Professional guide:  
24 Hours Professional online customer service,

