



24 ชั่วโมง บริการทุกวัน !!
!! บริการทุกวัน 24 ชั่วโมง .บริการทุกวัน !!

Diode Laser

For You. For Life.



0000 0000000 00000 00000 000 1064 755808 0000

- 1) 0000 0000000 TEC 0 000 0 0000 24 0000 000 00000000 0000 000000 00 00 0000 0 0000 000000 000000 000000 .000000 00
- 0000 0000 40.000.000 0 00000000 00 0000000000 0000000 000000 00000 00000000 (2
- .00000000 000000 00000 00000 0 0000000 0000000 00000 00000 0 0000000 (3
- 000000 00000000 0000 0000000 0000 0000000 0 00000 00000 0 0000 1600 000000 00000 0000 (4.

350g lightweight **handle**, more ergonomic

Available in **black or white**



755808 1064 1000 10 20 * 12 1000 1000

1000 1000 10 20 * 12 1000 1000.

.1000 1200 12 35 * 12 1000 1000
1000 1600 16 35 * 12 1000 1000.

1000 1000 1000 1000 1000

1000 1000 1000 1000 1000 1000 1000 1000 1000 1000



755808 1064 1064nm 1064nm 1064nm 1064nm 1064nm 1064nm




1) 1064nm 1064nm 1064nm 1064nm 1064nm 1064nm

2) 1064nm 1064nm 1064nm 1064nm 1064nm 1064nm 1064nm 1064nm
1064nm 1064nm 1064nm 1064nm 1064nm 1064nm 1064nm 1064nm (3.



0000 0000 0000 000 0 00000 000000 00000








□□□□ □□□□

1. 14 □□□□ □□□□ □ □□□□ □□□□□ □□□□ □□□□
2. □□□□□ □□□□□ 6 □ □□□□ □□□□□ □ □□□□ / □□□□
3. □□□□ □□□□ □□□□□□□□□□ □□□□□
4. OEM □□□□ / □□□□□) □□□□□□□□□□...

The new **14-inch 4K** screen

Support system customization



特點及優點

輕便型	重量 1064 公克 808 公克 755 公克
輕便型 輕便	16 - 8 吋 輕便 輕便
輕便型 輕便	100 公克
輕便型 輕便	14 吋 輕便型 輕便型 輕便型 輕便型
輕便型 輕便型	808 公克 1064 公克 755 公克 808 公克 輕便型
輕便型 輕便	12 * 35 吋 20 * 12 / 吋
輕便型 輕便 輕便	808 公克 4000000-10000000 公克 輕便 輕便 :輕便型
輕便	10-150 公克 2 公克 / 150 公克) 輕便型 輕便 2 公克 / 公克)
輕便型 輕便	40 ~ 800ms 輕便型 輕便
輕便型	1.0-10 公克
輕便型 輕便	輕便型 輕便型 TEC 輕便 輕便 輕便 輕便
輕便型 輕便 輕便型	800 公克 1600 / 公克 1200 / 公克 1000 / 公克
輕便型 輕便	2000 公克
輕便型 輕便	220 公克 60 / 公克 110 公克 50 / 公克
輕便型 輕便 輕便	-10 ~ 3 公克 公克
輕便型 輕便 輕便	27 ~ 31 公克 公克
輕便型 輕便型	AC220V / 110V 50 ~ 60 公克

輕便型 輕便 輕便型 輕便型 輕便型