



One minute cooling -27°C

Best TEC Cooling system
hair remover laser

2-특징

- * 피부에 자극 없이 냉각 효과를 극대화하여 통증 없이 안전하게 레이저를 사용할 수 있습니다.
- * 피부에 자극 없이 냉각 효과를 극대화하여 통증 없이 안전하게 레이저를 사용할 수 있습니다.
- * 피부에 자극 없이 냉각 효과를 극대화하여 통증 없이 안전하게 레이저를 사용할 수 있습니다.

12*24mm or 12*36mm handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...




3-

1.Alex 755nm


2.Speed Diode 808nm

3- 1064



Hair removal comparison

The real picture taken by the customer
 Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

Hair removal comparison

The real picture taken by the customer

Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

4. OEM / ODM

1. OEM / ODM 14 .1

2. OEM / ODM 6 6 6 .2

3. OEM / ODM 6 .3

4. OEM / ODM (OEM / ODM...)

5. OEM / ODM

>>OEM your own machine body

>>OEM your own program software

>>OEM pretty machine colors

>>Print your LOGO on machine body and screen

>>R & D team and Quality inspection Show

6. OEM / ODM

Build more trusted partners

Our customers

60000+ CUSTOMERS

OEM/ODM

Customize the machine according to customer needs



CERTIFICATE

Obtained multi-way authoritative certification, product testing certification, product patent authority,



7. 运输方式

运输方式 3-7 天
 运输方式 3-7 天

! 运输方式 3-7 天 24 !!