



.
 .
 *
 *
 *
 *
 *
 *

350g

Ultra light handle



12×36mm

Handle

1800W diode laser hair removal




12×24 mm

Handle

1200W diode laser hair removal

Three Waves 755 1064 808

755 . (/) .
 . 808
 1064nm () .




ALEX 755nm
For white skin
 (fine, golden hair removal)




SPEED 810nm
For yellow neutral skin
 (brown hair removal)



YAG 1064nm
For black skin
 (black hair removal)



Treatment Comparison



1. 100% 無痛
 2. 100% 無傷
 3. 100% 無副作用
 4. 100% 無痛
 5. 100% 無傷
 6. 100% 無副作用
 7. 100% 無痛
 8. 100% 無傷
 9. 100% 無副作用

1. 100% 無痛
 2. 100% 無傷
 3. 100% 無副作用
 4. 100% 無痛
 5. 100% 無傷
 6. 100% 無副作用
 7. 100% 無痛
 8. 100% 無傷
 9. 100% 無副作用



15 Years Laser Beauty Decvice Manuafactor

Make your beauty business easier

本公司 15 年來，致力於研發和生產各類激光美容設備，為全球客戶提供優質的解決方案。我們擁有先進的生產設備和技術，確保產品質量卓越。歡迎各界人士垂詢合作。

1. 產品種類齊全，覆蓋各類美容需求。

2. 技術研發實力雄厚，不斷推出新穎產品。

3. 完善的售後服務體系，確保客戶滿意。

Premium OEM Factories

High-performance manufacturing capacity
 R&D capability for customization
 Professional certifications and approvals



OEM 10000 0 00000000 ODM:

- .0000 00 000000
- 000000 0000 -
- .000000 00000 0000 0000 00 0000 -
- .000000 00 00000000 0000000000 0000000 00000 0 00 00000 0000 0000 0000 -
- 0000000000 00 00000000 00000 00000000 0 0000000 00000 000000 0000000 0000000 -.

Packing

Safe and thoughtful packaging service



Tight packaging

The machine shall be made of waterproof materials and packaged

Anti collision foam board inside aluminum box



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service

Professional guide: 24 Hours Professional online customer service!