

New Machine

“

**High power diode laser
with nice cooling technology**
for hair removal with painless!

”





* 1800W High power diode laser with nice cooling technology for hair removal with painless!

* The machine is designed for professional use in clinics and spas. It features a large touchscreen display for easy operation and a built-in cooling system to ensure a painless treatment.

* The machine is equipped with a high-quality laser source and a precision cooling system, ensuring optimal results and patient comfort.

* The machine is designed for professional use in clinics and spas. It features a large touchscreen display for easy operation and a built-in cooling system to ensure a painless treatment.



808 nm for yellow neutral skin (brown hair removal);

1064 nm for black skin (black hair removal)

Page 10 of 10

1. 0000 0000 0000 0000.
- 2-0000 000 40.000.000 000000 00000000 0000000 00 000000 00 0000000 000000 000000.
- 3.00000 0 00000 0000 000000 0000
4. 000000 000000 000000 000000 000000 000000
- 5.14.0 0000000 000000 6 00 000000000 000000000 0000000 00000 00000.

Three Wavelengths Work Togher



755nm Laser
808nm Laser
1064nm Laser



808nm

755nm



755nm Laser
808nm Laser
1064nm Laser



808nm

755nm

755.0nm 光照射 (照射時間 / 照射面積 100mm²) による光照射 照射時間 808 1064nm 光照射 (照射時間 照射面積) による光照射.

For all skin types

Triple wavelength laser work together

755
nm

808
nm

1064
nm

755nm/808nm/1064nm

755nm
808nm
1064nm

Laser hair removal treatment theory



Hair active growth
phase(3-6years)



laser treatment



Transition phase
(1-2weeks)



Resting phase
(1-2 weeks)



Return to growth
phase

□□□□□ **Parameters**







808 29	808 29
808	808 808 808 3 755/808/1064
14 4	14 4 K 755/808/1064
20-40	20-40
10 ~ 150	10 ~ 150 2 /
1-10	1-10
3500	3500
12 * 24	12 * 24 36 * 12
110	110 50 / 220 60 /
95	95
105	105
53 * 40 * 105	53 * 40 * 105

□□□□ □□□

125 * 56 * 70.4

Before and After



Before



After



Before



After



Before



After



Before



After

□□□□□□ □□□□□□ □□□□□□ □□□□□□ □□□□□□ □□□□ □□□□ □ □□□ □□□□ □□□□□□!

□□□□□□ □□□□□

* □□□□□ 14.0 □□□□□

* □□□□□□□ □□□□□□ □□□□□

* □□□□□□□□□□ □□□□□□□□ □□□□□□□ □□□□□□ - □□□□□□□□ □□□□□□


* □□□□ □□□□□□□ □□□□□□□ □□□□□□ □□□□□ SCR

Custom Section

LOGO design



SYSTEM design



0000000000 00000 00000000 000000 0000 000000 000000

Our customers

60000+ CUSTOMERS



102

Countries

OEM/ODM

Customize the machine according to customer needs

CERTIFICATE



PACKING

Safe and thoughtful packaging service



Built-in prevention
collision bubble

Two- year warranty for machine
handle as consumable,
one-year warranty

Tight packaging

Training:
(video +manual+online service)
can keep you operate it easily



3-5 business days
delivery

professional guide:
24 hours professional online
customer service