


DIODE LASER HAIR REMOVAL MACHINE


LEARN MORE



* 00000000 00 00000000 00000000 00000 000000 00000000 00 000000 000000000 00000000 00000 000000
000000 00000000 0000000000 00000000 0 00000000 00 000000000000 00000 00000000 00 000000 000000 . 000000

* 000000 000000 000000 0000000000 000000 0000 000000 00 0000 000000 000 0000 000000
000000 00000 0000 0000 0000000000 0000000000

* 0000 000 .00000 0000 0000 000000 000 !!! 0000 00 .0000 10-1 000000!!



808 nm for yellow neutral skin (brown hair removal);

1064 nm for black skin (black hair removal)

1. 00000000 00000000 00 00000000 00 00000000 00000000 000000-2 .0000 0000 000000 000000
3 .0000 000 40.000.000 00000000 0000000000.Safe 0 000000 000000 .4 0000 0 0000 000 0 0000
00000000 000000 6 00 0000000000 0000000000 00000000 000000 000000 0000 5.14.0 00000000 000000 000000.

Handle Details

Three Wavelengths Work Togher



□□□□ □□□□ **Waves 755nm 808nm 1064nm** □ □□□□□ □□□□□□ □□□□□□ □□□□ □□□□ □□□□ □□.

755 .□□□□□ □□□□□□ (□□□□□□□ / □□□□□□□ □□□□□□) □□□□□□□ □□□□□□□ □□□□□□□
.(□□□□□□□□) □□□□□□□ □□□□□ □□□ □□□□□□□ □□□□□□□ 808
1064nm □□□□□ □□□□□□□ (□□□□□□□ □□□□□□) □□□□□□□□ □□□□□□□.

For all skin types

Triple wavelength laser work together

755
nm

808
nm

1064
nm

755nm/808nm/1064nm

755nm
808nm
1064nm

Laser hair removal treatment theory



Hair active growth
phase(3-6years)



laser treatment



Transition phase
(1-2weeks)



Resting phase
(1-2 weeks)



Return to growth
phase

□□□□□ **Parameters**







808 29	29
808	808
14 4	14 4
755/808/1064	755/808/1064
20-40	20-40
10 ~ 150	10 ~ 150
1-10	1-10
3500	3500
12 * 24	12 * 24
110	110
95	95

□□□□□

105 □□□

$$53 * 40 * 105 \square\square$$
$$125 * 56 * 70.4$$

□ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □

○○○○○○ ○○○○○○ ○○○○○○ ○○○○○○ ○○○○○○ ○○○○○○○ ○○○○ ○○○○ ○ ○○○ ○○○○ ○○○○○○ ○○○○○○!

□□□□□ □□□□ □□□

* □□□□ 14.0 □□□□

* □□□□□ □□□□□ □□□□

* 00000000 00000000 00000000 000000 00000 - 00000000 00000

* □□□ □□□□□□ □□□□□□ □□□□□□ □□□□□ □□□□ SCR

Custom Section



□ □ □ □ □ □ □

□□□□□□□□ □□□□ □□□□□□ □□□□ □□□□ □□□□ □□□□

☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐	☐
--------------------------	--------------------------	--------------------------	--------------------------	--------------------------	--------------------------	--------------------------	--------------------------	--------------------------	--------------------------	--------------------------	--------------------------

Our customers

60000+ CUSTOMERS



102

Countries

OEM/ODM

Customize the machine according to customer needs

CERTIFICATE



14 我们拥有 102 个国家 60000+ 客户 102 个国家 60000+ 客户！

13 我们拥有 102 个国家 60000+ 客户

我们拥有 CE 认证 我们拥有 TÜV 认证

我们拥有 102 个国家 60000+ 客户 我们拥有 102 个国家 60000+ 客户

我们拥有 102 个国家 60000+ 客户

我们拥有 102 个国家 60000+ 客户 我们拥有 102 个国家 60000+ 客户 我们拥有 102 个国家 60000+ 客户

我们拥有 102 个国家 60000+ 客户！

PACKING

Safe and thoughtful packaging service



Built-in prevention
collision bubble

Two- year warranty for machine
handle as consumable,
one-year warranty

Tight packaging

Training:
(video +manual+online service)
can keep you operate it easily



3-5 business days
delivery

professional guide:
24 hours professional online
customer service