



DIODE LASER HAIR REMOVAL

PAINLESS HAIR REMOVAL, NO SIDE EFFECT

MORE



Diode Laser
Permanent hair removal

□□□□□□□□ □□□□□□ □□□□□□ □□□□□□ □□□□□□ □□□□ □□□□ □□□□

1. □□□□□□ □□□□□□ □□□□ □□□□ □□ □□□□□□ □□ □□□□□□ 15 □□ □□□□ □□□□□□ .□□□□□□.
2. □□□□ □□□ □ □□□□□□□ □□□□□□ □□□□□□ □□□□ □□ □□□□□□ □□□□ □□ .□□□□□□□□.
3. □□□□ □□□□ □□□□□□ □□□□□□ □□□□ □□□□ □□□□□□.
4. □□□□□□ □□□□□□ □ □□□□□□□□ 1064 □□□□□□□□□□ 808 □□□□□□□□□□ 755 :□□□□□□□□ □□□□□□ □□□□□□ .□□□□□□□□ □□□□□□ □□□□□□□□ □□□□□□ □□□□□□ □□□□□□ □□□□ □□□□□□ □□□□□□ □□□□□□.
5. □□□□□□ □ □□□□□ □□□□ □□□□□□ □□□□□□ □□□□ □ □□□□ □□□□□□ 50 □ □□□□□□□□ □□□□□□□□ □□□□ .□□□□□□ □□□□ □□□□ □□□□ □□□□□□.

□□□□□□ □□□□

12*24mm or 12*36mm handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...



- >>> Big 20*12 □□□□□□ □□□□mm, 12*35mm for option
- >>> Laser technology, big power 10bar 1200W, 12 bar 1800W
- >>> 300g handle, light weight, free quick slide treatment



>>> New nose hair treatment head, applicable to small part treatment
>>> 1 minute refrigeration frosting, painless treatment experience






ALEX 755nm
For white skin
(fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)



غرض	عمودي 755 نانومتر 808 نانومتر 1064 نانومتر ليزر ديود
نوع الليزر	شريط ليزر طبي ليزر ديود: 10 بار / 15 بار
قوة كل شريط	طبي مع 120 واط / بار
نظام العرض	بوصة تعمل باللمس اللون الحقيقي 14
الطول الموجي	نانومتر / 755 نانومتر / 1064 نانومتر 808
Spot Size	طبي بقطر 12 * 24 مم / 12 * 36 مم ²
عمر مقبض الليزر	ما لا يقل عن 40 مليون طلقة
طاقة	(جول / سم 2 قابل للتعديل) حتى 150 جول / سم 2 اختياري 10-150
مدة النبض	قابل للتعديل 30 ~ 400ms
تكرار	هرتز 1.0-10
نظام التبريد	كومبريسور هواء دوران ماء مغلق
التعامل مع القوة	واط / 1200 واط / 1600 واط / 1800 واط 1000
قوة الآلة	واط 4000
مصدر كهربائي	فولت / 50 هرتز أو فولت / 110 فولت / 60 هرتز 220
درجة حرارة الكريستال	درجة مئوية 3 ~ -20
درجة حرارة الآلة	درجة مئوية 24
متطلبات الطاقة	هرتز 60 ~ 50 110V / AC220V

□□□□□□ □□□





15 Years Laser Beauty Decvice Manuafactor

Make your beauty business easier

OEM 10000 1 10000000 ODM:

- .000 00 000000
- 00000 000 -
- .000000 00000 0000 000 00 0000 -
- .000000 00 00000000 0000000000 000000 00000 0 00 00000 0000 0000 0000 -

..... 1064 755808

Premium OEM Factories

High-performance manufacturing capacity
R&D capability for customization
Professional certifications and approvals



..... 1064 755808

..... 24!