


“

“



* 0000 000 .00000 0000 00000 00000 000 !!! 0000 00 .0000 10-1 000000!!



755 nm for white skin (fine, golden hair removal);

808 nm for yellow neutral skin (brown hair removal);



1064 nm for black skin (black hair removal)

□ □ □ □ □ □ □ □ □

[illegible]

Handle Details

Three Wavelengths Work Togher



□□□□ □□□□ **Waves 755nm 808nm 1064nm** □ □□□□□ □□□□□□ □□□□□ □□□□ □□□□ □□□□ □□□□□□.

755 .□□□□□ □□□□□□ (□□□□□□ / □□□□□□ □□□□□□) □□□□□□□□ □□□□□□□□ □□□□□□□□□□
(□□□□□□□□□□) □□□□□□□ □□□□□ □□□ □□□□□□□ □□□□□□□□ 808
1064nm □□□□□ □□□□□□□ (□□□□□□□ □□□□□□□) □□□□□□□□ □□□□□□□□.

For all skin types

Triple wavelength laser work together

755
nm

808
nm

1064
nm

755nm/808nm/1064nm

755nm
808nm
1064nm

Laser hair removal treatment theory



Hair active growth
phase(3-6years)



laser treatment



Transition phase
(1-2weeks)



Resting phase
(1-2 weeks)



Return to growth
phase

□□□□□ **Parameters**







808 29	mm
808	mm 3 755/808/1064 mm mm mm
14 4	mmK mm mm
755/808/1064	
20-40	mm mm
10 ~ 150	mm 2 /
1-10	mm
mm mm	mm
3500	mm
12 * 24	mm 36 * 12 mm
110	mm 50 / mm 220 mm mm 60 / mm
95	mm

重量 105 kg
 体高 185 cm
 体围 53 * 40 * 105 cm
 体脂率 12.5 * 56 * 70.4
 体脂肪量 13.1 kg

Before and After



Before



After



Before



After



Before



After



Before



After

体脂肪率 12.5% 体脂肪量 13.1kg 体脂肪率 12.5% 体脂肪量 13.1kg 体脂肪率 12.5% 体脂肪量 13.1kg

体脂肪率 12.5% 体脂肪量 13.1kg

体脂肪率 12.5% 体脂肪量 13.1kg

* 体脂肪率 14.0% 体脂肪量 13.1kg

* 体脂肪率 12.5% 体脂肪量 13.1kg

* 体脂肪率 12.5% 体脂肪量 13.1kg 体脂肪率 12.5% 体脂肪量 13.1kg - 体脂肪率 12.5% 体脂肪量 13.1kg

* 体脂肪率 12.5% 体脂肪量 13.1kg 体脂肪率 12.5% 体脂肪量 13.1kg SCR

Custom Section

LOGO design



SYSTEM design



□□□□ □□□
 □□□□□□□□□□ □□□□□ □□□□□□ □□□□□ □□□□ □□□□□ □□□□□□
 □□□□□□□□ □□□□□

Our customers

60000+ CUSTOMERS



102

Countries

OEM/ODM

Customize the machine according to customer needs

CERTIFICATE



14 我们拥有 102 个国家 60000+ 客户 我们拥有 102 个国家 60000+ 客户!

13 我们拥有 102 个国家 60000+ 客户

我们拥有 CE 认证 我们拥有 TUV 认证

我们拥有 102 个国家 60000+ 客户

我们拥有 102 个国家

我们拥有 102 个国家 60000+ 客户 我们拥有 102 个国家 60000+ 客户

我们拥有 102 个国家!

PACKING

Safe and thoughtful packaging service



Built-in prevention
collision bubble

Two- year warranty for machine
handle as consumable,
one-year warranty

Tight packaging

Training:
(video +manual+online service)
can keep you operate it easily



3-5 business days
delivery

professional guide:
24 hours professional online
customer service