

1000 W 1200 W 1600 W

Best **TEC Cooling** system hair remover laser

[illegible]


350g lightweight **handle**, more ergonomic

Available in **black or white**



>>1-10Hz fast □□□□□

>> Italy water pump, it can keep machine working 24 hours without stop.




Hair removal principle

Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area



Natural hair loss, prevent regeneration, and achieve the purpose of hair removal



Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth

Illegible text line 1

Illegible text line 2

Illegible text line 3



1. **Pre-treatment preparation**
 .Pre-treatment preparation 12.4 :Pre-treatment preparation (1)

.Pre-treatment preparation 6 (2)

2. **Post-treatment care** (3)

.Post-treatment care

.Post-treatment care

.Post-treatment care

.Post-treatment care

12inch 1200mm

40mm

Energy

Frequency

12 * 20mm

35 * 12mm

-10 ~ 3mm

AC220 / 110V 50/60Hz

12inch 1200mm

40mm

Energy

Frequency

12 * 20mm

35 * 12mm

-10 ~ 3mm

AC220 / 110V 50/60Hz

12 * 20mm

-10 ~ 3mm


AC220 / 110V 50/60Hz

Custom Section


CASE design



LOGO design



SYSTEM design



12 * 20mm

OUR TEAM

There are more than 100 members of production team in our factory.

A large group of approximately 30 factory workers, mostly men and women in white short-sleeved uniforms, are posing for a group photo in a spacious factory with a bright green floor. Many of the workers are holding up small green objects, possibly products or awards, in a celebratory gesture. The background shows industrial equipment, overhead lighting, and the vastness of the factory interior.

OUR TEAM

There are more than 100 members of production team in our factory.

A large group of approximately 30 factory workers, mostly men and women in white short-sleeved uniforms, are posing for a group photo in a spacious factory with a bright green floor. Many of the workers are holding up small green objects, possibly products or awards, in a celebratory gesture. The background shows industrial equipment, overhead lighting, and the vastness of the factory interior.

A modern medical device showroom with various machines and a large map of China on the wall. The room features a polished floor, a grid ceiling with recessed lights, and a large map of China on the wall. The machines are arranged in a row, and the overall atmosphere is clean and professional.

OUR COUNTRIES

All the products are taking with CE/ISO certification ,suitable for world market , mainly used on North America , South America Europe
60, 000+ Customers Business development in 102+ countries...

A modern medical device showroom with various machines and a large map of China on the wall. The room features a polished floor, a grid ceiling with recessed lights, and a large map of China on the wall. The machines are arranged in a row, and the overall atmosphere is clean and professional.

OUR COUNTRIES

All the products are taking with CE/ISO certification ,suitable for world market , mainly used on North America , South America Europe
60, 000+ Customers Business development in 102+ countries...

Weifang Mingliang Electronics Co., Ltd (簡體中文: MLKJ) 係一間於香港註冊之公司，其業務範圍包括製造及銷售電子產品。該公司之主要業務為生產及銷售各種電子元件，如電阻、電容、電感等。該公司之產品主要供應予電子製造業，如電腦、通訊設備、消費電子等。該公司之產品主要供應予電子製造業，如電腦、通訊設備、消費電子等。

我们是一家专业的电子产品包装公司。我们拥有专业的包装团队，可以根据客户的需求，提供定制化的包装方案。我们的包装方案，可以保证产品在运输过程中的安全，同时还可以提高产品的附加值。我们的包装方案，已经得到了广大客户的认可和好评。我们的包装方案，可以满足客户的需求，同时还可以提高产品的附加值。我们的包装方案，已经得到了广大客户的认可和好评。我们的包装方案，可以满足客户的需求，同时还可以提高产品的附加值。

1. Weifang Mingliangkj Electronics Co. , Ltd (简称: MLKJ) 是一家专业的电子产品包装公司，成立于15年前，主要从事电子产品包装、r & d、生产、销售、服务。我们的包装方案，可以保证产品在运输过程中的安全，同时还可以提高产品的附加值。我们的包装方案，已经得到了广大客户的认可和好评。我们的包装方案，可以满足客户的需求，同时还可以提高产品的附加值。

PACKING

safe and thoughtful packaging seivice



Tight packaging

Training:
(video +manual+online service)
can keep you operate it easily

Built-in prevention collision bubble

Two- year warranty for machine
handle as consumable,
one-year warranty



3-5 business days delivery

professional guide:
24 hours professional online
customer service

