

4 in 1





MULTI-FUNCTION 4 IN 1 MACHINE

□□□□□□□□ □□□

Real shot display



808 handle



Elight handle



ND YAG Laser handle



RF handle



□□□□ □□□□ Elight / IPL Nd yag RF □ 4 □□□□ □□□□ □□ □□□□□□ □□□□□
1 □□ 4 □□□□ □□□□□ RF Elight IPL □□□□ □□□□□□□ □□□□□□ nd yag □□□□□□ □□□□□ □□□
□□□□ □□□□

* .□□□□ □□□□□ 50 □□□ □ □□□□□□□ □□ □□□□□□ □□□□ □□□□ □□□□ □□□□ □□□□
□□□□ □□□□□□ * Elight □□□□ 30□000 □□□ 150□000 □ □□□□□□□ □□□□□□ □□□□□

* Nd yag: 1064 □ □□□□□□ □□□□ 5 □□□□□nm / 532nm 1064 □ □□□□□□ □□□□□nm / 532nm □□□□□
1320 □nm □□□□□.

* RF: □□□□□ □□ □ □□□□□ □□ □ □□□□□□□ □□□□□□ □ □□□□□□ □□□□□ 6 □□□□□.

DIODE LASER

755/808/1064nm diode laser, for all type skin hair removal, painless



ADVANTAGE

- **PAINLESS:** 755/808/1064nm diode laser for all type skin hair removal
- **FASTER:** Large area spot sliding operation
- **NO TRAUMA:** There is no trauma to skin tissue
- **SAFETY:** To avoid the light of the deputy to reduce the difficulty of operation



Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.



• *Cooling effect* •

The handle is frosted for one minute,
making your treatment more comfortable and painless



Elight handle



specification

- High-quality: Elight handpiece with super cooling system
- Optional Spot Size 15*50mm
- Long shots time: 150000 times
- 7 filters: 420/510/560/585/640/690/755nm
Standard: 420/510/680nm



HANDLE-ADVANTAGE



specification

- **Multiple choice**
fixed 1064nm & 532nm, adjustable 1064nm & 532nm (adjust 1-7 mm) for tattoo removal, nevus removal etc.
- **Multifunction**
1320nm for skin rejuvenation
- **Indicator light**
Dot position is the indicator light position dot more accurate



Adjustable
532nm



Adjustable
1064nm



Black doll
1320nm



Fixed
532nm



Fixed
1064nm



Before&after compare



before



One cycle



Two cycles



Three cycles

Tattoo removal



Tattoo removal



Nevus of Ota removal



Tattoo on brow removal



Lioline removal



Lioline removal



Tattoo on brow removal



RF Handl^e



12mm
eye-rf

28mm small
tripolar rf head

36mm big
tripolar rf head

14mm
bipolar-rf

28mm
bipolar-rf

38mm
bipolar-rf

Skin rejuvenation/Vascular/Acne



before



after



before



after



before



after

BEFORE & AFTER [®]



Hair removal



Skin rejuvenation



Freckle removal



Acne removal



Vascular



Lose weight

SCREEN INTERFAC [®]

Professional Screen, Easy operation



14	10-300
1-10	Elight: 15 * 50
20 * 12	20 * 12 :mm & 12 * 35mm
1-150	1-150 2 /
TEC	TEC

额定电压 额定功率	AC220V / 110 额定 60 / 额定 50 额定
demension 额定	113 * 65 * 76
额定	额定 额定
额定	额定

额定 额定





Authentication

CE, NQA13485, CB certification
and more Complete certification
materials



60000+ Customers

We have professional after sale
team and we provide 7*24
services



2 Years Warranty

2 years warranty for each
machine, All questions will get
reponse within 24 hours



CERTIFICATE DISPLAY



3: 3

5-3

4: 4

5: 5

6: 6

7: 7

8: 8

9: 9

10: 10

11: 11

12: 12

13: 13

14: 14