



1. 0000 0000 00000 00000.
2. 0000 000 40.000.000 0 000000 0000000000 0000000 00000000 00 0000000 00 00000000 0000000 000000 0000000 00000 00000 00000 00000 00000.3
- 00000 00000 00000 000000 000000 000000 .4
- 5.14.0 000000 00000 6 00 000000000 0000000000 0000000 00000 0000.
6. 000000 0000 00 0000 0000 0 000000000 0000000 00000

One minute cooling -21°C

Best **TEC Cooling** system hair remover laser



- 1) 10 .mmmm mmmm 40-10 m mmm 16 / mmm 12 / mmm
.mmmm mmmm mmmm mmm 35 * 12 / mmm 20 * 12 mmmm mmm (2
mmm mmm mmmm mmmm m mmmm mmmm mmmm mmmm mmm (3.
4) mmmm mmm mmmm mmmm mmm mmm mmm mmm.
5) mmmm mmm mmm 350 mmm mmm mmm mmm mmm.



1 minute
and you're done

35mm {

FASTER

000000 0000



1. 14 .
 .
 .
 .
 .

16 12 10 8	nm 808nm 1064nm / 808 nm
755nm 808nm 1064nm / 808 nm	
0-150 2	
1-10	
40-800	
LCD 14.0 TFT True Color LCD	
4000	
220 60 / 110 50 /	
NW / GW	62 78 /

**Standardized
production**



**Professional
Production R & D
Sales Department**



**Mass production
of various styles**



- >>OEM your own machine body.
- >>OEM your own program software.
- >>OEM pretty machine colors.
- >>Print your LOGO on machine body and screen.

Custom Section


CASE dedign



LOGO design



SYSTEM design



CERTIFICATE DISPLAY

