

NEW PRODUCT

D10

Portable Hair Removal Machine

-Convenient and efficient hair removal-





☎️ 1064 755808 ☎️
☎️ 1064 755808 ☎️

Working Principle

Suits for all skin and hair types




12*20nm
755nm Laser
808nm Laser
1064nm Laser



- **755nm for white skin** (fine, golden hair removal)
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)

□□□□□□□□ □□□

Mini Portable

The net weight of the handle is
about equal to one iphone

285g



Ergonomic handle
It's not tiring to take off

□□□□□□ □□□

□□□□ □□□□□□□□ □□□ 1800 / □□□ 1200 □□□□□□ □□□

□□ 36 * 12 □□ 24 * 12 □□□□□□ □□□

* 285 □□□□□□ □□□□□□□□ □□□□ □□□□ □□□□ □□□□ □□□□

* □□□□□ □□□□□□ □ (□□□□□□□□ □□□□□□ □□□□) □□□□□ □□□□□□ □□□□ □□□□ □□

□□□□□□ □□□□□ □□□□□ □□□□□ □□□□□ □□□□□ □□□□□ □□□□□ □□□□□

What can **we do** in **1 MINUTE**

Time for a cup of instant coffee,
the handle can quickly frost.



Product parameters



Device Name	Diode Laser Machine
Model Number	Diode Laser D10
Wavelength	755+808+1064nm Technology
Screen size	12inch 4K-HD screen
Lifetime	50 Million shots
Pulse Duration	10-300ms
Laser Bar	100w for each one America Coherent Laser Bar
Frequency	1-10hz
Spot size	12x20mm Spot Size
Energy	1-150J
Cooling System	TEC cooling circulation
Power Of Machine	2500W
Voltage	AC220V 50HZ/60HZ
Demension of machine	380mm*460mm*300mm
Package	Aluminum box
Warranty	2 years for machine 1 year for handle

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable, one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

7 * !!!!!!!!!!!!!!! 24 !!!!!!!
!!!!!!!!!!!!!! !!!!!!!