

MLKJ

CUSTOMER SERVICE

15 YEARS FACTORY, 2 YEARS WARRANTY, 102 COUNTRIES, 60,000+ CUSTOMERS.

MLKJ—MAKE YOUR BEAUTY BUSINESS EASIER



15 years factory



2 years warranty



102 COUNTRIES



2 years warranty




14 inch
Screen Size



3000W
Input power



1-10HZ
Frequency



755nm 808nm 1064nm
Wavelength

>>Machine 14-inch large screen

>>3000 W machine power to ensure the treatment effect

>>1-10 Hz fast frequency and 15x25mm treatment spot ensures faster, smooth and effective treatment

>>808 single wave or 755nm/808nm/1064nm perfect triple wavelength systems

>>Easy to operate Data Base system,can do the treatment by man mode and women mode, easy to operate

□□□□□□ □□□□□□ □□□□ □□□□□□ □□□□□□ □□ □□□□□□

>> Long life time More than 40 millions □□□□□□ gold laser diode module, anti high temperature.

350g lightweight **handle**, more ergonomic

Available in **black or white**



□□□□□□ □□□□□□ □□□ □ □□□ □□□□□□□□ **350** □□□□□□□□ □□□□

>>12 pcs or 16 pcs Germany Dilas original laser bars,600/800W/1200W power is capable to meet all demands of hair removal on the whole body;

>>1-10Hz fast frequency and 15x25mm spot size ensures faster, smooth and effective treatment;
 >Super sapphire touch 系统 ensures painless and comfortable treatment;




Hair removal principle


Make Your Beauty Business More Easier





The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area



Natural hair loss, prevent regeneration, and achieve the purpose of hair removal



Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth



- 755 nm for white skin (fine, golden hair removal);
- 808 nm for yellow neutral skin (brown hair removal);
- 1064 nm for black skin (black hair removal)

系统 系统 40-20 系统 系统 系统 系统

系统 系统 系统 系统 系统 系统 系统 :系统 808 系统
 Alex 755nm: 系统 系统 系统 系统 系统 系统
 系统 系统 系统 系统 系统 系统 系统 :系统 1064 系统 系统 ipl shr opt / nd yag / alexandrite 系统 系统 系统 系统








品牌	808V27- 品牌 品牌
品牌 品牌	808nm 品牌 3 755/808/1064 品牌 品牌 品牌
品牌	品牌 14 品牌 品牌 品牌 品牌 品牌
Wavelength	808 1064 808 755 / 品牌
shots	20-40 品牌 品牌
品牌	10 ~ 150 品牌 品牌 品牌 2 品牌 / 品牌
Frequency	1-10HZ
Cooling	品牌 品牌 TEC
Power	3000W
Spot size	12 * 35 品牌 品牌 20 * 12 品牌 品牌
品牌 品牌	110 品牌 品牌 50 / 品牌 220 品牌 品牌 60 / 品牌

品牌 品牌

1. 品牌 品牌 Weifang Mingliang 品牌 品牌 品牌 品牌 品牌 品牌 品牌 15 品牌 品牌.

600000 102



2.Support OEM OEM

3.R & D

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

□□□□ □□ □□□□
□□□□□□□□ □□ □□□□ 24!