



1. CE ISO13485
 2. CE ISO13485
 3. CE ISO13485
 4. CE ISO13485
 5. CE ISO13485
 6. CE ISO13485
 7. CE ISO13485
 8. CE ISO13485
 9. CE ISO13485
 10. CE ISO13485



1. .
- 1000 :2W 1200 W 20 * 12 mm 35 * 12 mm
3. 10-1 :Hz . 12 TEC 4
- 24 °C

1000 1000W 1200 1600

One minute cooling -27°C

Best TEC Cooling system hair remover laser



1000 1000W 1200 1600

1000 1000W 1200 1600 20 * 1.12

1000 1000W 1200 1600 35 * 2.12

1000 1000W 1200 1600 .3

350g lightweight **handle**, more ergonomic

Available in **black or white**




>>Germany Emitter, strong

1200<<W power of hair removal on the whole body;

>>1-10Hz fast

>> Italy water pump, it can keep machine working 24 hours without stop.



755nm

More powerful energy absorption by the melanin chromophore, making it ideal for the widest range of hair types and color
- especially light-colored and thin hair

808/810nm

Deep penetration of the hair follicle with high average power with high repetition rate for fast treatment. moderate melanin absorption level making it safe for darker skin types.
ideal for treating the arms, legs, cheeks and beard.

1064nm


low melanin absorption, focused solution for darker skin types. Offers the deepest penetration of the hair follicle, embedded hair in areas as the scalp, armpit, and pubic area.

Hair removal principle

Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area



Natural hair loss, prevent regeneration, and achieve the purpose of hair removal



Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth

1. The laser energy is absorbed by the melanin in the hair follicle, which is the primary target for destruction.

2. The hair follicle is destroyed, and the hair shaft is broken through the skin surface.

3. The hair follicle is shrunk, and the surrounding skin tissue is stimulated to regenerate collagen, making the skin firmer and smoother.



□□□□□□ □□□□



The new 14-inch screen is clear
easy to operate.



OEM/ODM SEVRICE

3D LOGO with luxurious texture.

1). 12.4 inch screen : 12.4 inch screen

. 6 (2)

12 inch screen : 12 inch screen (3)

12 inch

12 inch screen

12 inch

12 inch screen

12 inch

12 inch screen : 12 inch screen 1000 10 1200 12 inch

12 inch

12 inch screen

12 inch

12 inch screen

Energy

10 ~ 150 12 inch screen

12 inch

40 ~ 800ms 12 inch screen

Frequency

1 ~ 10 12 inch

TEC 1200 12 inch

12 inch

12 inch screen

12 inch screen

12 inch screen

12 inch

12 * 20 35 * 12 12 inch

12 inch

-10 ~ 3 12 inch

12 inch


AC220 / 110 50/60 12 inch

Custom Section


CASE design



LOGO design




SYSTEM design



000000 0000

OUR TEAM

There are more than 100 members of production team in our factory.



PACKING

safe and thoughtful packaging service



Built-in prevention
collision bubble

Two- year warranty for machine
handle as consumable,
one-year warranty

Tight packaging

Training:
(video +manual+online service)
can keep you operate it easily



3-5 business days
delivery

professional guide:
24 hours professional online
customer service