



1. CE ISO13485
 2. CE ISO13485
 3. CE ISO13485
 4. CE ISO13485
 5. CE ISO13485
 6. CE ISO13485
 7. CE ISO13485
 8. CE ISO13485
 9. CE ISO13485
 10. CE ISO13485



1. .
 2. .
 3. 10-1 :
 4. 1200 :
 5. 1200 :
 6. 1200 :
 7. 1200 :
 8. 1200 :
 9. 1200 :
 10. 1200 :

1000 W 1200 W 1600 W

Best **TEC Cooling** system hair remover laser



00000 00 00000 00000 .000 00000 0 00000 00000 0 0000000000 00000000 0000000000 00 0000000000 0000000 00000 00 00000000 0000000 0000000


350g lightweight **handle**, more ergonomic

Available in **black or white**



>>1-10Hz fast □□□□□

>> Italy water pump, it can keep machine working 24 hours without stop.




Hair removal principle

Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area



Natural hair loss, prevent regeneration, and achieve the purpose of hair removal



Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth

0000000000 00 000000 00000000 000000 0 000000 000000 000000 000000 0000 0000 00000000 000000.

00000000 00000000 00000000 00 000000 00000000 00000000 00

000000 000000 00000000 0 0000000000 0 00000000 000000 0 0000000000 0 00000000 0 000000 000000.



1. 12.4 : 1
 2. 6 (2
 3. 3
 4.

1. 12.4 : 1
 2. 6 (2
 3. 3
 4.

1. 12.4 : 1
 2. 6 (2
 3. 3
 4.

1. 12.4 : 1
 2. 6 (2
 3. 3
 4.

1. 12.4 : 1
 2. 6 (2
 3. 3
 4.

12inch 1200mm

Energy

Frequency

12 * 20mm 35 * 12mm

Energy

Frequency

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12inch 1200mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

Custom Section

CASE design




12 * 20mm 35 * 12mm

LOGO design



SYSTEM design




OUR TEAM

There are more than 100 members of production team in our factory.



OUR COUNTRIES

All the products are taking with CE/ISO certification ,suitable for world market ,
mainly used on North America ,
South America Europe
60, 000+ Customers Business development
in 102+ countries...



Customer visit



mingliangkj:

Weifang Mingliang Electronics Co., Ltd (MLKJ) 13 years of experience in the field of medical equipment.

Our products are widely used in hospitals, clinics, and research institutions. We have a strong R&D team and a complete production system. Our products are of high quality and reliable performance.

Our products are widely used in hospitals, clinics, and research institutions. We have a strong R&D team and a complete production system. Our products are of high quality and reliable performance.

Our products are widely used in hospitals, clinics, and research institutions. We have a strong R&D team and a complete production system. Our products are of high quality and reliable performance.

1. (MLKJ) 13 years of experience in the field of medical equipment.

2. r & d team and complete production system.

3. Our products are of high quality and reliable performance.

PACKING

safe and thoughtful packaging service



Built-in prevention
collision bubble

Two- year warranty for machine
handle as consumable,
one-year warranty

Tight packaging

Training:
(video +manual+online service)
can keep you operate it easily



3-5 business days
delivery

professional guide:
24 hours professional online
customer service