



1. CE ISO13485
 2. CE ISO13485
 3. CE ISO13485
 4. CE ISO13485
 5. CE ISO13485
 6. CE ISO13485
 7. CE ISO13485
 8. CE ISO13485
 9. CE ISO13485
 10. CE ISO13485
 11. CE ISO13485
 12. CE ISO13485
 13. CE ISO13485
 14. CE ISO13485
 15. CE ISO13485
 16. CE ISO13485
 17. CE ISO13485
 18. CE ISO13485
 19. CE ISO13485
 20. CE ISO13485
 21. CE ISO13485
 22. CE ISO13485
 23. CE ISO13485
 24. CE ISO13485
 25. CE ISO13485
 26. CE ISO13485
 27. CE ISO13485
 28. CE ISO13485
 29. CE ISO13485
 30. CE ISO13485
 31. CE ISO13485
 32. CE ISO13485
 33. CE ISO13485
 34. CE ISO13485
 35. CE ISO13485
 36. CE ISO13485
 37. CE ISO13485
 38. CE ISO13485
 39. CE ISO13485
 40. CE ISO13485
 41. CE ISO13485
 42. CE ISO13485
 43. CE ISO13485
 44. CE ISO13485
 45. CE ISO13485
 46. CE ISO13485
 47. CE ISO13485
 48. CE ISO13485
 49. CE ISO13485
 50. CE ISO13485
 51. CE ISO13485
 52. CE ISO13485
 53. CE ISO13485
 54. CE ISO13485
 55. CE ISO13485
 56. CE ISO13485
 57. CE ISO13485
 58. CE ISO13485
 59. CE ISO13485
 60. CE ISO13485
 61. CE ISO13485
 62. CE ISO13485
 63. CE ISO13485
 64. CE ISO13485
 65. CE ISO13485
 66. CE ISO13485
 67. CE ISO13485
 68. CE ISO13485
 69. CE ISO13485
 70. CE ISO13485
 71. CE ISO13485
 72. CE ISO13485
 73. CE ISO13485
 74. CE ISO13485
 75. CE ISO13485
 76. CE ISO13485
 77. CE ISO13485
 78. CE ISO13485
 79. CE ISO13485
 80. CE ISO13485
 81. CE ISO13485
 82. CE ISO13485
 83. CE ISO13485
 84. CE ISO13485
 85. CE ISO13485
 86. CE ISO13485
 87. CE ISO13485
 88. CE ISO13485
 89. CE ISO13485
 90. CE ISO13485
 91. CE ISO13485
 92. CE ISO13485
 93. CE ISO13485
 94. CE ISO13485
 95. CE ISO13485
 96. CE ISO13485
 97. CE ISO13485
 98. CE ISO13485
 99. CE ISO13485
 100. CE ISO13485



1. .
 2. .
 3. 10-1
 4. 1000 :
 5. 1200 :
 6. 20 * 12
 7. 35 * 12
 8. 10-1
 9. 1000 :
 10. 1200 :
 11. 20 * 12
 12. 35 * 12
 13. 10-1
 14. 1000 :
 15. 1200 :
 16. 20 * 12
 17. 35 * 12
 18. 10-1
 19. 1000 :
 20. 1200 :
 21. 20 * 12
 22. 35 * 12
 23. 10-1
 24. 1000 :
 25. 1200 :
 26. 20 * 12
 27. 35 * 12
 28. 10-1
 29. 1000 :
 30. 1200 :
 31. 20 * 12
 32. 35 * 12
 33. 10-1
 34. 1000 :
 35. 1200 :
 36. 20 * 12
 37. 35 * 12
 38. 10-1
 39. 1000 :
 40. 1200 :
 41. 20 * 12
 42. 35 * 12
 43. 10-1
 44. 1000 :
 45. 1200 :
 46. 20 * 12
 47. 35 * 12
 48. 10-1
 49. 1000 :
 50. 1200 :
 51. 20 * 12
 52. 35 * 12
 53. 10-1
 54. 1000 :
 55. 1200 :
 56. 20 * 12
 57. 35 * 12
 58. 10-1
 59. 1000 :
 60. 1200 :
 61. 20 * 12
 62. 35 * 12
 63. 10-1
 64. 1000 :
 65. 1200 :
 66. 20 * 12
 67. 35 * 12
 68. 10-1
 69. 1000 :
 70. 1200 :
 71. 20 * 12
 72. 35 * 12
 73. 10-1
 74. 1000 :
 75. 1200 :
 76. 20 * 12
 77. 35 * 12
 78. 10-1
 79. 1000 :
 80. 1200 :
 81. 20 * 12
 82. 35 * 12
 83. 10-1
 84. 1000 :
 85. 1200 :
 86. 20 * 12
 87. 35 * 12
 88. 10-1
 89. 1000 :
 90. 1200 :
 91. 20 * 12
 92. 35 * 12
 93. 10-1
 94. 1000 :
 95. 1200 :
 96. 20 * 12
 97. 35 * 12
 98. 10-1
 99. 1000 :
 100. 1200 :

1000 1200 1600 W

One minute cooling -27°C

Best TEC Cooling system hair remover laser



20 * 1.12

35 * 2.12

3

350g lightweight **handle**, more ergonomic

Available in **black or white**




>>Germany Emitter, strong

1200<<W power of hair removal on the whole body;

>>1-10Hz fast



>> Italy water pump, it can keep machine working 24 hours without stop.



755nm

1064nm

Hair removal principle



0000000000 00 000000 000000 000000 0 000000 000000 000000 000000.0000 000 000000 000000.

12inch 1200mm

Energy

Frequency

12 * 20mm 35 * 12mm

Energy

Frequency

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12inch 1200mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

12 * 20mm 35 * 12mm

Custom Section


CASE design



LOGO design



SYSTEM design



12 * 20mm 35 * 12mm


OUR TEAM

There are more than 100 members of production team in our factory.



OUR COUNTRIES

All the products are taking with CE/ISO certification ,suitable for world market ,
mainly used on North America ,
South America Europe
60, 000+ Customers Business development
in 102+ countries...



Customer visit



mingliangkj:

1. Weifang Mingliangkj Electronics Co., Ltd (MLKJ) 15
 .2 r & d
 -3.

PACKING

safe and thoughtful packaging service



Built-in prevention
collision bubble

Two- year warranty for machine
handle as consumable,
one-year warranty

Tight packaging

Training:
(video +manual+online service)
can keep you operate it easily



3-5 business days
delivery

professional guide:
24 hours professional online
customer service