

EXFU Redefine hair removal equipment
Simple - Safe - Enjoy
SIMPLE SAFE ENJOY




□□□□

□ □□ □□□□□□ □□□ ROHS □CE □□□□□□□

□ 3 □□□□ □□□□ □□ □□□□ □□□□□□ □□□□ - 1 □□
□ □□□□□□□ □□□□□□□□ □□□□□ □ Nd:YAG - □□□□□□ □□□□□ □□□□□□
□□□□□□□ □□□ □
□□□□□□□ □□□□□□ □□□□ □
□□□□ □□□ □□□□ □□□□□ 50 □!

□□□□□ □□ □□□□□□□□

Ergonomic design



Comfortable
painless hair removal



Mild cooling
No irritation



ICE

ONLY 350G
HANDLE

Medical diode laser

50000000+shots
can treat 10000+clients

- *Not easy to be burned
- *Low maintenance cost
- *Stable quality



* 1000 shots per treatment

* Low maintenance cost. The device is designed for long-term use with minimal downtime.

* 1064 nm wavelength, 808 nm pump, 755 nm emission. The device is designed for high efficiency and stability.

* 150 J/cm²/cm² * 12 treatments per session. The device is designed for high energy output and stability.

Before and After

Treatment comparison



1. 3-0 3-2
2. 3-2
3. Real-5C



EXFU

OEM&ODM Professional Design

