



1. CE ISO13485
 2. CE ISO13485
 3. CE ISO13485
 4. CE ISO13485
 5. CE ISO13485
 6. CE ISO13485
 7. CE ISO13485
 8. CE ISO13485
 9. CE ISO13485
 10. CE ISO13485



1. .
 2. .
 3. .
 4. .
 5. .
 6. .
 7. .
 8. .
 9. .
 10. .

000000 000 00000 0 °C 24 00000000

00000000 0000 000000000 000000 000000 00000 00000 00 0000 0 000000 00000 00000 00000

1000 00000000 000000 000000 0000**W 1200** 00**W 1600** 00**W**

One minute cooling -27°C

Best **TEC Cooling** system hair remover laser



000000000000 000000000 000000 000000 00000 00000

000000000 00 00000000 000000 0000 000000 0000 0 000000 00 000000 000000 0000 00 20 * 1.12 00 0000000000 0000000

.0000000000

00000000 000000000 000000 0000 0 000000 00 000000 000000 0000 00 35 * 2.12 000000000 00000

00000 00 00000 00000 .0000 00000 0 00000 00000 0 00000000000 000000000 000000000 0000000000 000000 0000 00 .3

000000000 000000 0000000

350g lightweight **handle**, more ergonomic

Available in **black or white**




>>Germany Emitter, strong 00000

1200<<W power of hair removal on the whole body;

>>1-10Hz fast 00000

>> Italy water pump, it can keep machine working 24 hours without stop.




Hair removal principle

Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area



Natural hair loss, prevent regeneration, and achieve the purpose of hair removal



Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth

0000000000 00 000000 00000000 000000 0 000000 000000 000000 000000 0000 0000 00000000 000000.

00000000 0000000 0000000 00 00000 0000000 000000 00

000000 00000 00000000 0 0000000000 0 0000000 000000 0 000000000000 00000000 0 000000000 0 00000 00000.



1. 12.4 : 6 (1)
 2. 6 (2)
 3. (3)

12inch 1200mm

Energy

Frequency

10 ~ 150

40 ~ 800ms

1 ~ 10

TEC 1200

12 * 20 35 * 12

-10 ~ 3

AC220 / 110

50/60

12inch 1200mm

Energy

Frequency

10 ~ 150

40 ~ 800ms

1 ~ 10

TEC 1200

12 * 20 35 * 12

-10 ~ 3

AC220 / 110

50/60

Custom Section


CASE design



LOGO design



SYSTEM design



12inch 1200mm



OUR TEAM

There are more than 100 members of production team in our factory.

OUR COUNTRIES

All the products are taking with CE/ISO certification ,suitable for world market ,
mainly used on North America ,
South America Europe
60、000+ Customers Business development
in 102+ countries...

潍坊 mingliangkj:

潍坊 Weifang Mingliang Electronics Co. , Ltd (简称: MLKJ) 专业生产 各种 美容仪器 美容设备 美容用品 美容工具 美容材料 美容配件 美容耗材 美容辅料 美容包装 美容宣传 美容培训 美容咨询 美容服务 美容代理 美容加盟 美容合作 美容批发 美容零售 美容进出口 美容跨境电商 美容线上线下 美容全渠道 美容新零售 美容新营销 美容新渠道 美容新平台 美容新场景 美容新体验 美容新服务 美容新品牌 美容新形象 美容新文化 美容新未来

潍坊 Mingliang Electronics Co. , Ltd 是一家专业从事美容仪器、美容设备、美容用品、美容工具、美容材料、美容配件、美容耗材、美容辅料、美容包装、美容宣传、美容培训、美容咨询、美容服务、美容代理、美容加盟、美容合作、美容批发、美容零售、美容进出口、美容跨境电商、美容线上线下、美容全渠道、美容新零售、美容新营销、美容新渠道、美容新平台、美容新场景、美容新体验、美容新服务、美容新品牌、美容新形象、美容新文化、美容新未来

