

DIODE LASER hair removal machine

■ 2 Years Warranty ■ OEM / ODM Service ■ 3 waves 1064nm +808nm + 755nm



DIODE LASER hair removal machine **D10**

* 12—8 treatment sessions per treatment area. Treatment area depends on the treatment area.

* Treatment area depends on the treatment area. Treatment area depends on the treatment area. 3 treatment sessions per treatment area. 50 treatment sessions.

* 3 treatment sessions per treatment area. Treatment area depends on the treatment area. 1 treatment session per treatment area. 3 treatment sessions per treatment area. 755 treatment sessions. 808 treatment sessions. 1064 treatment sessions.

Handle Display

Two colors, two spot sizes are optional



1064nm 808nm 755nm :suitable for all skin types

755nm suitable for all skin types.

808nm suitable for all skin types.

1064nm suitable for all skin types.

Working Principle

755nm and 808nm and 1064nm , suits for all skin and hair types.



ALEX 755nm
For white skin
(fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)

The real experience is visible

Through live test verification ,safe ,long,painless
and effective



- 1) .00000 14 000000 00000 0000 0000 :000000 00000
- .00000000 000 0 0000000 000000 00 000000 000000 00000 00000 (2
- 00000 (3 OEM: 00000000 00000 000000 0 00000000 00000000 00000 0000 000000 000000 000000.



Product details

Ultra-thin large screen, cool light strip



!!!!!!! !!!!!!! !!!!!!! !!!!!!! !!!!!!!
!!!!!! !!!!!!! 24!