



V28: ມີສາມ ສະໜັບສະໜູນ ສະໜັບ ສະໜູນ ສະໜັບ

1) ສະໜັບ ສະໜັບ ສະໜັບ ສະໜັບ ສະໜັບ

2) ສະໜັບສະໜູນ 1064 ສະໜັບສະໜູນ 810 ສະໜັບສະໜູນ 755 ສະໜັບ ສະໜັບສະໜັບ ສະໜັບສະໜັບ ສະໜັບ

3) 40 ສະໜັບ ສະໜັບ ສະໜັບ 800/1000/1200/1600 ສະໜັບ




weight 450g
The handle weighs only 450g, making the treatment process easier

			
12*20mm	12*35mm	12*20mm	12*35mm

1. 35 * 12 / 20 * 12 2. 35 * 12 / 20 * 12 3. 35 * 12 / 20 * 12 4. 35 * 12 / 20 * 12
 5. 35 * 12 / 20 * 12 6. 35 * 12 / 20 * 12 7. 35 * 12 / 20 * 12 8. 35 * 12 / 20 * 12

Laser show Handle laser bar optional



1064nm 808nm 755nm
 1064nm 808nm 755nm
 1064nm 808nm 755nm

10bar 12bar 16bar


1. 1064 808 755 2. 1064 808 755 3. 1064 808 755 4. 1064 808 755
 5. 1064 808 755 6. 1064 808 755 7. 1064 808 755 8. 1064 808 755
 9. 1064 808 755 10. 1064 808 755 11. 1064 808 755 12. 1064 808 755
 13. 1064 808 755 14. 1064 808 755 15. 1064 808 755 16. 1064 808 755
 17. 1064 808 755 18. 1064 808 755 19. 1064 808 755 20. 1064 808 755
 21. 1064 808 755 22. 1064 808 755 23. 1064 808 755 24. 1064 808 755



Just One minute!
Quick cooling down to **-25°C**



Treatment Comparison



000000 000 000 000000

000000 0000 0 000000 0000 0000 14 .1

0000000 000000000 0000000 000000 00 000000 6 0 000000 00 000000 6 0 000000 00000 6 .2

0000 00000 000000 00000 0 00000 0000000 6 .3

0000000 00000 .4 OEM 000000 / 00000000 / 00000000 / 0000000) 00000000...)

FREE LOGO SERVICE





14 Years Laser Beauty Decvice Manuafactor

- High Feedback **Top10 Supplier**
- **OEM & ODM SERVICE**



1. 我们拥有14年的激光美容设备生产经验，产品远销全球102个国家。
 2. 我们拥有完善的质量管理体系，产品出厂前经过严格检测，确保质量。
 3. 我们拥有专业的研发团队，可根据客户需求定制各种规格的产品。

Certificate display

Certificate is the best guarantee for you



Parameters



品牌名称	品牌名称 V28.0
品牌名称 品牌	品牌 12 品牌 10 品牌 品牌 品牌 品牌 品牌 品牌 / 品牌 品牌 品牌 16 品牌
品牌	14 ---- 15.6 4 品牌K 品牌 品牌
品牌名称 品牌名称	755 品牌名称 1064 品牌名称 808 品牌名称
品牌名称	40 品牌 品牌
品牌名称	10 ~ 150 品牌名称 品牌 2 品牌 / 品牌
品牌名称	1-10 品牌
品牌名称	品牌名称 TEC 品牌 品牌
品牌	3500 品牌
品牌名称 品牌	12 * 20mm / 12 * 35mm 品牌名称
品牌名称 品牌名称	110 品牌名称 品牌 50 / 品牌 220 品牌 品牌 60 / 品牌
品牌名称 品牌名称	95 品牌
品牌名称 品牌名称	105 品牌
品牌名称 品牌	45 * 52 * 110 品牌
品牌名称 品牌	56 * 70.4 * 125 品牌
品牌名称 品牌 品牌 品牌	7-3 :品牌名称 品牌
品牌 品牌 品牌 品牌	:品牌名称 品牌名称 DHL 品牌 TNT 品牌 Fedex 品牌名称 品牌 品牌
品牌名称 品牌名称 品牌名称	:品牌名称 品牌
品牌名称 品牌 品牌名称 品牌 品牌 品牌 品牌	:品牌名称 品牌 品牌 品牌
品牌名称 品牌名称 品牌	

Packing

Safe and thoughtful packaging service



Tight packaging

The machine shall be made of waterproof materials and packaged

**Anti collision foam board
inside aluminum box**



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service

CONTACT US



In terms of following trade details:

- 1)The shipping cost are based on DHL cost to your country
- 2)Delivery time:3-5 days after receiving payments.
- 3)Payment terms:T/T(bank transfer),Western Union.
- 4)Warranty:2 years for the whole machine
- 5)Warranty Policy:one month guarantee replacement (we bear all shipping cost),2years warranty,lifelong maintenance.
- 6)Packing method: Aluminum box with hard plastic foam.
- 7)Free-training to customers:Free We could offer DVD and User's manual and 10 Hours online service to our customers
- 8)Certifications:CE TUV SFDA ISO 13485
- 9)MOQ:1 UNIT
- 10)The quotation here above is valid within 1 month