



1. CE ISO13485
 2. CE ISO13485
 3. CE ISO13485
 4. CE ISO13485
 5. CE ISO13485
 6. CE ISO13485
 7. CE ISO13485
 8. CE ISO13485
 9. CE ISO13485
 10. CE ISO13485



1. 1000 : 2W 1200 Hz 20 * 12 mm 35 * 12 mm
 3. 10-1 : 1000 Hz 20 * 12 mm 35 * 12 mm
 4. TEC 12

000000 0000 00000 0 °C 24 00000000

00000000 00000 000000000 0000000 000000 00000 000000 000 0000 0 0000000 000000 000000 00000

1000 000000000 0000000 000000 0000**W 1200** 000**W 1600** 000**W**

One minute cooling -27°C

Best **TEC Cooling** system hair remover laser



000000000000 000000000 0000000 0000000 00000 00000

000000000 00 00000000 0000000 0000 0000000 0000 0 0000000 00 0000000 0000000 0000 00 20 * 1.12 00 0000000000 00000000
.0000000000

00000000 0000000000 0000000 0000 0 0000000 00 0000000 0000000 00 00 35 * 2.12 0000000000 000000

000000 00 00000 000000 .0000 000000 0 000000000000 0000000000 0000000000 00 0000000000000 00000000 000000 0000 00 .3
0000000000 0000000 0000000

350g lightweight **handle**, more ergonomic

Available in **black or white**




>>Germany Emitter, strong 00000

1200<<W power of hair removal on the whole body;

>>1-10Hz fast 00000

>> Italy water pump, it can keep machine working 24 hours without stop.




Hair removal principle

Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area



Natural hair loss, prevent regeneration, and achieve the purpose of hair removal




Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth

0000000000 00 000000 00000000 000000 0 000000 000000 000000 000000 0000 0000 00000000 000000.

00000000 00000000 000000 00 000000 000000 000000 00

000000 000000 00000000 0 0000000000 0 00000000 00000000 0 0000000000 0 0000000000 0 000000 000000.



WALTZ PRO LASER

1	2	3

000000 0000




0000000000 00000000 000000 000000 0000 0000
 .00000000 0000 0000 12.4 :00000000 0000 0000 (1
 .0000000000 000 6 (2

AC220 / 110 □□□□ 50/60 □ □□□□

Custom Section


CASE design



LOGO design




SYSTEM design



000000 0000

OUR TEAM

There are more than 100 members of production team in our factory.



PACKING

safe and thoughtful packaging service



Built-in prevention
collision bubble

Two- year warranty for machine
handle as consumable,
one-year warranty

Tight packaging

Training:
(video +manual+online service)
can keep you operate it easily



3-5 business days
delivery

professional guide:
24 hours professional online
customer service