

3) 35mm 350mm 350mm 350mm 350mm 350mm (3.

4) 350mm 350mm 350mm 350mm 350mm 350mm.

5) 350mm 350mm 350mm 350mm 350mm 350mm.



1 minute
and you're done

35mm

FASTER

350mm 350mm

1. 14 .350mm 350mm 350mm 350mm 350mm 350mm

.350mm 350mm 6 350mm 350mm 350mm / 350mm .2

.350mm 350mm 350mm 350mm 350mm 6 .3

350mm 350mm .4 OEM 350mm / 350mm) 350mm...)

350mm 350mm

350mm 16 350mm 12 350mm 10 350mm 8 350mm 350mm 350mm 350mm / 350mm

350mm 350mm

755nm 808nm 1064nm / 808 350nm 350mm

350mm

0-150 2 350mm / 350mm

350mm

1-10 350mm

350mm 350mm

40-800 350mm 350mm

350mm 350mm LCD

14.0 350mm TFT True Color LCD 350mm 350mm

350mm 350mm

350mm 350mm 350mm 350mm 350mm 350mm 350mm 350mm 350mm 350mm 350mm 350mm 350mm 350mm 350mm

350mm 350mm

350mm 350mm

350mm

4000 350mm

□□□□□□ □□□□ 220 □□□□ 60 / □□□□ 110 □□ □□□□ 50 / □□□□
 NW / GW 62 □□□□ 78 / □□□□



**Standardized
 production**



**Professional
 Production R & D
 Sales Department**




**Mass production
 of various styles**

- >>OEM your own machine body.
- >>OEM your own program software.
- >>OEM pretty machine colors.
- >>Print your LOGO on machine body and screen.

Custom Section


CASE dedign



LOGO design



SYSTEM design



□□□□□□ □□

CERTIFICATE DISPLAY

